

# Grooved IPS Pipe Couplings

EFFECTIVE NOVEMBER 3, 2009

## AGS<sup>®</sup> Rigid Coupling

### AGS STYLE W07

Request publication 20.02.



14 – 24"



26 – 60"

### AGS STYLE W07 – GRADE "E" OR "T" FLUSHSEAL GASKET

PIPE		Aprx. Wgt. Ea	COUPLING COMPLETE † With FlushSeal <sup>®</sup> "E" or "T" Gasket		SPARE PARTS	
Inches			Price Each		Plated Bolt & Nut	
Nom. Size	Outside Dia.	Lbs.	Painted	Galv.	No. *	Size § Inches
14	14.000	48.9	<b>\$479.75</b>	\$615.25	2	1 x 5½
16	16.000	60.8	<b>624.75</b>	797.25	2	1 x 5½
18	18.000	71.2	<b>722.00</b>	935.50	2	1 x 5½
20	20.000	81.7	<b>986.50</b>	1236.25	2	1½ x 5½
24	24.000	116.2	<b>1265.25</b>	1602.75	2	1½ x 5½
26	26.000	205.0	<b>2287.25</b>	+	4	1¾ x 6
28	28.000	220.0	<b>2725.75</b>	+	4	1¾ x 6
30	30.000	227.0	<b>3820.75</b>	+	4	1¼ x 7
32	32.000	242.0	<b>4174.50</b>	+	4	1¼ x 7
36	36.000	268.0	<b>4503.25</b>	+	4	1¼ x 7
40	40.000	340.0	<b>5390.75</b>	+	4	1½ x 7
42	42.000	360.0	<b>6006.50</b>	+	4	1½ x 7
46	46.000	415.0	<b>6379.75</b>	+	4	1½ x 7
48	48.000	425.0	<b>6639.50</b>	+	4	1½ x 7
54	54.000	648.0	<b>8656.75</b>	+	4	1½ x 7
56	56.000	676.0	<b>9206.25</b>	+	4	1½ x 7
60	60.000	720.0	<b>10305.75</b>	+	4	1½ x 7

§ Metric thread size bolts available. Contact Victaulic.

NOTE: See Spare Parts Section for spare part prices.

+ Quoted on application. Contact Victaulic for pricing and availability.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

# Grooved IPS Pipe Couplings

## AGS<sup>®</sup> Rigid Coupling

### AGS STYLE W07

Request publication 20.02.



14 – 24"



26 – 60"

### AGS STYLE W07 – SILICONE GRADE "L" FLUSHSEAL GASKET

PIPE		Aprx. Wgt. Ea.	COUPLING COMPLETE † With FlushSeal Silicone Grade "L" Gasket		SPARE PARTS	
Inches			Price Each		Plated Bolt & Nut	
Nom. Size	Outside Dia.		Painted	Galv.	No.	Size § Inches
14	14.000	48.9	\$1204.00	\$1339.50	2	1 x 5½
16	16.000	60.8	1324.50	1497.00	2	1 x 5½
18	18.000	71.2	1456.50	1670.25	2	1 x 5½
20	20.000	81.7	1688.50	1938.25	2	1½ x 5½
24	24.000	116.2	1839.50	2177.00	2	1½ x 5½
26	26.000	205.0	2659.50	+	4	1¾ x 6
28	28.000	220.0	3025.00	+	4	1¾ x 6
30	30.000	227.0	3920.00	+	4	1¾ x 7
32	32.000	242.0	4263.25	+	4	1¾ x 7
36	36.000	268.0	4619.75	+	4	1¾ x 7
40	40.000	340.0	5514.50	+	4	1½ x 7
42	42.000	360.0	6128.00	+	4	1½ x 7
46	46.000	415.0	6640.75	+	4	1½ x 7
48	48.000	425.0	6921.00	+	4	1½ x 7
54	54.000	648.0	+	+	4	1½ x 7
56	56.000	676.0	+	+	4	1½ x 7
60	60.000	720.0	+	+	4	1½ x 7

§ Metric thread size bolts available. Contact Victaulic.

NOTE: See Spare Parts Section for spare part prices.

+ Quoted on application. Contact Victaulic for pricing and availability.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

# Grooved IPS Pipe Couplings

## AGS Flexible Coupling

### AGS STYLE W77 – GRADE “E” OR “T” FLUSHSEAL GASKET

#### AGS STYLE W77

Request publication 20.03.



14 – 24”



26 – 60”

PIPE		Aprx. Wgt. Ea.	COUPLING COMPLETE † With FlushSeal® “E” or “T” Gasket		SPARE PARTS	
Inches			Price Each		Plated Bolt & Nut	
Nom. Size	Outside Dia.	Lbs	Painted	Galv.	No. *	Size ‡ Inches
14	14.000		47.5	\$494.25	\$682.75	2
16	16.000	57.8	648.25	879.50	2	1 x 5½
18	18.000	65.0	758.75	1052.25	2	1 x 5½
20	20.000	82.3	1013.50	1360.00	2	1½ x 5½
24	24.000	106.8	1308.00	1756.75	2	1½ x 5½
26	26.000	205.0	2307.25	+	4	1½ x 6
28	28.000	220.0	2790.25	+	4	1½ x 6
30	30.000	227.0	3870.75	+	4	1¼ x 7
32	32.000	242.0	4246.00	+	4	1¼ x 7
36	36.000	268.0	4553.25	+	4	1¼ x 7
40	40.000	340.0	5446.00	+	4	1½ x 7
42	42.000	360.0	6036.50	+	4	1½ x 7
46	46.000	415.0	6427.75	+	4	1½ x 7
48	48.000	425.0	6699.50	+	4	1½ x 7
54	54.000	648.0	8801.00	+	4	1½ x 7
56	56.000	676.0	9266.25	+	4	1½ x 7
60	60.000	720.0	10365.75	+	4	1½ x 7

‡ Metric thread size bolts available. Contact Victaulic.

NOTE: See Spare Parts Section for spare part prices.

**NOTE: 14 - 60” standard for this size range is the W77 AGS flexible coupling. For cut groove systems requiring the original groove coupling contact Victaulic for details.**

+ Quoted on application. Contact Victaulic for pricing and availability.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

# Grooved IPS Pipe Couplings

## AGS Flexible Coupling

### AGS STYLE W77

Request publication 20.03.



14 - 24"



26 - 60"

### AGS STYLE W77 - SILICONE GRADE "L" FLUSHSEAL GASKET

PIPE		Aprx. Wgt. Ea.	COUPLING COMPLETE † With FlushSeal Silicone Grade "L" Gasket		SPARE PARTS	
Inches			Price Each		Plated Bolt & Nut	
Nom. Size	Outside Dia.	Lbs	Painted	Galv.	No.	Size § Inches
14	14.000	47.5	\$1218.50	\$1407.00	2	1 x 5½
16	16.000	57.8	1347.75	1579.25	2	1 x 5½
18	18.000	65.0	1493.25	1736.00	2	1 x 5½
20	20.000	82.3	1715.25	2062.00	2	1½ x 5½
24	24.000	106.8	1917.75	2331.25	2	1½ x 5½
26	26.000	205.0	2757.25	+	4	1½ x 6
28	28.000	220.0	3133.00	+	4	1½ x 6
30	30.000	227.0	3997.75	+	4	1¼ x 7
32	32.000	242.0	4348.00	+	4	1¼ x 7
36	36.000	268.0	4643.25	+	4	1¼ x 7
40	40.000	340.0	5565.00	+	4	1½ x 7
42	42.000	360.0	6136.50	+	4	1½ x 7
46	46.000	415.0	6529.75	+	4	1½ x 7
48	48.000	425.0	6849.50	+	4	1½ x 7
54	54.000	648.0	8960.00	+	4	1½ x 7
56	56.000	676.0	9525.50	+	4	1½ x 7
60	60.000	720.0	10695.00	+	4	1½ x 7

§ Metric thread size bolts available. Contact Victaulic.

NOTE: See Spare Parts Section for spare part prices.

+ Quoted on application. Contact Victaulic for pricing and availability.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

### FOR STYLE W07/W77 AGS GASKETS

Nom. Size Inches	FlushSeal Grade "E" or "T" Gasket	Grade "L" Silicone Gasket
14	\$157.00	\$926.50
16	216.25	996.25
18	261.00	1041.25
20	401.00	1147.00
24	556.00	1166.50
26	699.50	1315.50
28	748.00	1405.50
30	796.50	1498.50
32	845.00	1588.50
36	938.50	1771.00
40	1036.00	1954.00
42	1084.50	2047.00
46	1162.50	2228.50
48	1213.00	2319.50
54	1436.00	2596.00
56	1483.00	2685.50
60	1580.50	2868.00

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. BOX 31, EASTON, PA 18044-0031 • 4901 KESSLERSVILLE ROAD, EASTON, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (FAX) • PICKVIC@VICTAULIC.COM

For complete contact information, visit [www.victaulic.com](http://www.victaulic.com)

PL2008-C-Main-ADD-W07W77 5924 REV A

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

PL2008-C-Main-ADD-W07W77

