

FireLock System for Grooved IPS Pipe

EFFECTIVE MAY 1, 2009

Fire Protection Valves

Grooved End Butterfly Valve – Supervised OPEN

SERIES 705

(with weatherproof actuator)
Request publication 10.81.



Request Victaulic publication 10.01 for details.

SERIES 705 BUTTERFLY VALVE

Nominal Size	WRD – Pre-wired without Tap		WRD – Pre-wired with Tap	
	Inches	Aprx. Wgt. Each Lbs	Aprx. Wgt. Each Lbs	Price Each
2	8.2	\$530.75	8.2	\$583.00
2½	9.7	530.75	9.7	583.00
76.1 mm	9.7	+	9.7	+
3	10.7	573.75	10.7	630.00
4	14.0	601.50	14.0	659.50
5	25.4	901.75	–	–
6	28.7	854.75	28.7	929.50
165.1 mm	28.7	+	28.7	+
8	43.0	1310.00	43.0	1399.75
10	80.6	3173.50	–	–
12	94.6	4533.00	–	–

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Weatherproof Actuator Replacement Kit

FOR SERIES 705 – SUPERVISED OPEN ONLY

(Consists of mounting bolt, actuator, handwheel and assembly hardware)
Request publication 10.81.

GEAR OPERATOR REPAIR KIT FOR SERIES 705

Nominal Size inches	Part Code	Kit Price Each
2 – 3	K024705100	\$393.00
4 – 5	K040705100	422.25
6	K060705100	459.25
8	K080705100	1086.75
10 – 12	K100705100	1414.25

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

FireLock System for Grooved IPS Pipe

Grooved End Butterfly Valve – Supervised CLOSED

SERIES 707C

(with weatherproof actuator)
Request publication 10.75.



Request Victaulic publication 10.01 for details.

SERIES 707C – PRE-WIRED

Nominal Size	WRD – Pre-wired without Tap		
	Inches	Aprx. Wgt. Each Lbs	Part Code
2	8.2	V020707900	\$530.75
2½	9.7	V024707900	530.75
76.1 mm	9.7	+	+
3	10.7	V030707900	573.75
4	14.0	V040707900	601.50
5	25.4	V050707900	901.75
165.1 mm	28.7	+	+
6	28.7	V060707900	854.75
8	43.0	V080707900	1310.00

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Grooved End High Pressure Butterfly Valve – Supervised OPEN

SERIES 765

(with Weatherproof Actuator)
Request publication 10.80.



SERIES 765 GROOVED END HIGH PRESSURE BUTTERFLY VALVE

Nominal Size	Pre-wired without Tap		Pre-wired with Tap	
	Inches	Aprx. Wgt. Each Lbs	Price Each	Aprx. Wgt. Each Lbs
2	8.2	\$595.00	8.2	\$645.75
2½	9.7	615.75	9.7	668.25
76.1 mm	9.7	+	9.7	+
3	10.7	665.75	10.7	722.25
4	14.0	697.75	14.0	757.25
5	25.4	1046.25	–	–
165.1 mm	28.7	+	28.7	+
6	28.7	991.75	28.7	1076.00
8	43.0	1519.75	43.0	1648.75
10	87.0	3681.50	–	–
12	103.0	5258.50	–	–

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

FireLock System for Grooved IPS Pipe

Grooved End High Pressure Butterfly Valve – Supervised CLOSED

SERIES 766

(with Weatherproof Actuator)
Request publication 10.83.



SERIES 766 GROOVED END HIGH PRESSURE BUTTERFLY VALVE

Nominal Size	Pre-wired without Tap		Pre-wired with Tap	
	Inches	Aprx. Wgt. Each Lbs	Aprx. Wgt. Each Lbs	Price Each
2	8.2	\$595.00	8.2	\$645.75
2½	9.7	615.75	9.7	668.25
76.1 mm	9.7	+	9.7	+
3	10.7	665.75	10.7	722.25
4	14.0	697.75	14.0	757.25
5	25.4	1046.75	-	-
165.1 mm	28.7	+	28.7	+
6	28.7	991.75	28.7	1076.00
8	43.0	1519.75	43.0	1648.25

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

FireLock System for Grooved IPS Pipe

Commercial Zone Control Riser Module

SERIES 747M

Request publication 10.96.



Request Victaulic publication 10.01 for details.

SERIES 747M – COMMERCIAL ZONE CONTROL RISER MODULE

Riser Module Body Size	Drain Size	Aprx. Wgt. Each	Price Each
Nominal Inches	Inches	Lbs	Style 747M Grooved *
1¼	1	15.2	\$600.00
1½	1	15.5	612.50
2	1	19.9	641.50
2½	1¼	22.7	693.25
3	1¼	23.2	727.75
4	2	30.3	891.75
6	2	36.7	996.00

*Price includes all components pictured at left.

See Part Code Configuration Guide

Residential Zone Control Riser Module

SERIES 247

Request publication 10.97.



Request Victaulic publication 10.01 for details.

SERIES 247 – RESIDENTIAL ZONE CONTROL RISER MODULE

Riser Module Body Size	Drain Size	Aprx. Wgt. Each	Price Each
Nominal Inches	Inches	Lbs	Style 247M Grooved *
1	1	15.2	\$562.50
1¼	1	15.2	600.00
1½	1	15.5	612.50
2	1	19.9	641.50

See Part Code Configuration Guide

FireLock System for Grooved IPS Pipe

Pressure Relief Valve Kit

FOR SERIES 747M AND 247 RISER MODULES

Request publication 10.97.



SERIES 247 PRESSURE RELIEF VALVE KIT

Riser Module Body Size	Victaulic	Price
Nominal Inches	Part Code	Each
1 – 6	V000747K01	\$276.25

Part Code Configuration Guide

SERIES 247 AND SERIES 747M

Part Code Structure Example:

NOTE: A BBB CCC D E F G HHH can be filled in as: V 040 747 P F S U 056

1. "V040747PFSU056" denotes a S747M system riser module with standard trim, 4" Grooved inlet/4" grooved outlet/2" NPT Female drain; painted orange; UL/FM approved, and K5.6 orifice.

SERIES 247 AND 747M RISER MODULES PART CODE CONFIGURATION GUIDE

Code	Definition	Options
A	Class	V : Fluid Control Devices
BBB	Size (inlet x outlet x drain) Note 2 *	010 : 1" x 1" x 1" 012 : 1¼" x 1¼" x 1" 014 : 1½" x 1½" x 1" 020 : 2" x 2" x 1" 024 : 2½" x 2½" x 1¼" 030 : 3" x 3" x 1¼" 040 : 4" x 4" x 2" 060 : 6" x 6" x 2"
CCC	Series	247 : Series 247 Residential Riser Module 747 : Series 747M Commercial Riser Module
D	Finish	P : Painted in Orange color
E	Drain Type	G : Grooved Connection F : NPT Female Threaded Connection
F	Trim Selection	S : Standard Trim
G	Approved Agency	U : UL/FM C : ULC/FM
HHH	K Factor (Orifice) Note 3 *	028 (K2.8), 030 (K3.0), 035 (K3.5), 042 (K4.2), 049 (K4.9), 056 (K5.6), 069 (K6.9), 080 (K 8.0), 112 (K11.2), 140 (K14.0), 168 (K 16.8)

Notes

- Example: "V040747PFSU56" denotes a Series 747M Commercial Zone Control Riser Module painted in orange color; 4" grooved inlet/4" grooved outlet/2" grooved drain connection; standard trim; UL/FM approved; with K5.6 flow restrictor.
- Available sizes for Series 247 Residential Riser Modules : 010, 012, 014, 020
Available sizes for Series 747M Commercial Riser Modules : 012, 014, 020, 024, 030, 040, 060
- Approved K Factors for 1" to 2" Series 247 Residential Riser Modules : 028, 030, 035, 042, 049, 056
Approved K Factors for 1" to 2" Series 747M Commercial Riser Modules : 056
Approved K Factors for 2½" to 3" Series 747M Commercial Riser Modules : 056, 069, 080, 112
Approved K Factors for 4" to 6" Series 747M Commercial Riser Modules : 056, 069, 080, 112, 140, 168

FireLock System for Grooved IPS Pipe



TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. BOX 31, EASTON, PA 18044-0031 • 4901 KESSLERSVILLE ROAD, EASTON, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (FAX) • PICKVIC@VICTAULIC.COM

For complete contact information, visit www.victaulic.com

PL2008-C-FP-ADD3 5682 REV A

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

PL2008-C-FP-ADD3

