

AquaFlex Stainless Steel Sprinkler Fittings

EFFECTIVE FEBRUARY 1, 2010

Series AQU

Unbraided Flexible Hose Assembly with Bracket, Hose and 1/2" or 3/4" Reducer



Size	Aprx. Wgt. Ea.	Victaulic	Box	Price
Inches	Lbs.	Part No.	Quantity	Each
31 x 1/2"	3.19	A31HAQFBEE	10	\$45.00
	3.19	A31TAQFBEE	10	\$47.00
48 x 1/2"	3.34	A48HAQFBEE	10	\$54.00
	3.34	A48TAQFBEE	10	\$56.00
60 x 1/2"	3.69	A60HAQFBEE	10	\$60.50
	3.69	A60TAQFBEE	10	\$62.50
72 x 1/2"	4.19	A72HAQFBEE	10	\$68.00
	4.19	A72TAQFBEE	10	\$70.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Series AQB

Braided Flexible Hose Assembly with Bracket, Hose and 1/2" or 3/4" Reducer



Size	Aprx. Wgt. Ea.	Victaulic	Box	Price
Inches	Lbs.	Part No.	Quantity	Each
31 x 1/2"	3.49	A31HAQFBEB	10	\$61.00
	3.49	A31TAQFBEB	10	61.00
48 x 1/2"	3.99	A48HAQFBEB	10	67.00
	3.99	A48TAQFBEB	10	67.00
60 x 1/2"	4.19	A60HAQFBEB	10	74.00
	4.19	A60TAQFBEB	10	74.00
72 x 1/2"	4.29	A72HAQFBEB	10	81.00
	4.29	A72TAQFBEB	10	81.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

AquaFlex Stainless Steel Sprinkler Fittings

Series AQS

SUB-ASSEMBLIES – HOSES LESS BRACKETS

Request publication 10.85.



BRAIDED HOSE WITH BRANCH LINE NIPPLE AND REDUCER – NO BRACKET

UNBRAIDED HOSE WITH BRANCH LINE NIPPLE AND REDUCER – NO BRACKET

Size		Aprx. Wgt. Ea.	Victaulic	Box	Price
Inches		Lbs.	Part No.	Quantity	Each
Unbraided Hose Only					
31	x 1/2	1.90	A31HAQFBUE	10	\$38.50
	3/4	1.90	A31TAQFBUE	10	40.50
48	x 1/2	2.15	A48HAQFBUE	10	45.00
	3/4	2.15	A48TAQFBUE	10	47.00
60	x 1/2	2.40	A60HAQFBUE	10	51.00
	3/4	2.40	A60TAQFBUE	10	54.00
72	x 1/2	2.90	A72HAQFBUE	10	61.50
	3/4	2.90	A72TAQFBUE	10	63.50
Braided Hose Only					
31	x 1/2	2.20	A31HAQFBBE	10	\$51.00
	3/4	2.20	A31TAQFBBE	10	51.00
48	x 1/2	2.70	A48HAQFBBE	10	64.00
	3/4	2.70	A48TAQFBBE	10	64.00
60	x 1/2	2.90	A60HAQFBBE	10	71.00
	3/4	2.90	A60TAQFBBE	10	71.00
72	x 1/2	3.00	A72HAQFBBE	10	74.50
	3/4	3.00	A72TAQFBBE	10	74.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Series AQS

BRACKET SUB-ASSEMBLIES – BRACKET COMPONENTS, REDUCING NIPPLES, REDUCING ELBOWS, BRANCH LINE NIPPLES

Description	Size	Aprx. Wgt. Ea.	Victaulic	Box	Price
	Inches	Lbs.	Part No.	Quantity	Each
Bracket Subassembly	24	1.29	A000AQFBEE	10	\$21.00
	48	1.29	A000AQFB48	10	26.00
Bar Stock	25	0.50	A000AQFB25	10	5.50
	50	1.00	A000AQFB50	10	6.50
Middle Open-Gate Bracket	–	0.18	A000AQFB5Q	10	5.50
Tall End Bracket – Concealed or Flush	–	0.18	A000AQFEBT	10	6.50
Reducing Nipple – 5 1/2" Length	1/2"	0.65	A000AQFRNH	10	11.00
	3/4"	0.65	A000AQFRNT	10	11.00
Reducing Nipple – 9" Length	1/2"	1.05	A090AQFRNH	10	16.50
	3/4"	1.05	A090AQFRNT	10	16.50
Reducing Nipple – 13" Length	1/2"	1.55	A130AQFRNH	10	22.00
	3/4"	1.55	A130AQFRNT	10	+
90° Reducing Elbow – 4" Length	1/2"	0.70	A000AQFRE4	10	21.50
	3/4"	0.70	A000AQFRE6	10	21.50
90° Reducing Elbow – 6" Length	1/2"	1.00	A000AQFRE5	10	21.50
	3/4"	1.00	A000AQFRE7	10	21.50
Institutional Bracket	–	.025	A000AQFINB	10	6.50
Branch Line Nipple	–	.025	A000AQFBLN	10	11.00
Bracket Wing Nut Bolt	–	0.50	A000AQFWNB	500	.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. BOX 31, EASTON, PA 18044-0031 • 4901 KESSLERSVILLE ROAD, EASTON, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (FAX) • PICKVIC@VICTAULIC.COM

For complete contact information, visit www.victaulic.com

PL2008-C-FP-ADD4 5683 REV B

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2010 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

PL2008-C-FP-ADD4

