

FireLock® System for Grooved IPS Pipe

EFFECTIVE OCTOBER 15, 2009

FireLock EZ® Rigid Coupling

STYLE 009H

Request publication 10.61



Request Victaulic publication 10.01 for details.

STYLE 009H – GRADE “E” (TYPE A) GASKET

PIPE Inches		Aprx. Wgt. Ea.	COUPLING COMPLETE † with Grade “E” (Type A) Gasket		SPARE PARTS Grade “E” (Type A) Gasket
Nom. Size	Outside Dia.		Price Each		
		Lbs	Painted	Galv.	
1¼	1.660	1.4	\$32.50	\$39.50	\$27.00
1½	1.900	1.5	33.50	40.50	29.25
2	2.375	1.9	37.50	44.50	31.25
2½	2.875	2.1	43.25	52.25	34.25
3	3.500	2.3	50.00	61.50	39.25
4	4.500	2.9	70.50	84.75	52.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. BOX 31, EASTON, PA 18044-0031 • 4901 KESSLERSVILLE ROAD, EASTON, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (FAX) • PICKVIC@VICTAULIC.COM

For complete contact information, visit www.victaulic.com

PL2008-C-FP-ADD5 5886 REV A

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

PL2008-C-FP-ADD5

