


FireLock System for Grooved IPS Pipe

EFFECTIVE DECEMBER 7, 2009

FireLock Rigid Coupling

STYLE 005
Request publication 10.02.



  
Rubber Gasketed
Pipe Fittings 913H
Request Victaulic
publication 10.01 for details.

STYLE 005 – VIC-PLUS GRADE “E” (TYPE A) GASKET

PIPE Inches		COUPLING COMPLETE † With Vic-Plus § Grade “E” (Type A) Gasket			SPARE PARTS			
Nom. Size	Outside Dia.	Aprx. Wgt. Each Lbs	Price Each		Grade E (Type A) Gasket Only Price Ea.	Bolt & Nut *		
			Painted	Galv.		No.	Size inches/ millimeters	Price Each Pltd.
1¼	1.660	1.5	\$32.50	\$39.50	\$27.00	2	¾ x 2¼	7.25
1½	1.900	1.6	33.50	40.50	29.25	2	¾ x 2¼	7.25
2	2.375	1.9	37.50	44.50	31.25	2	¾ x 2½	8.00
2½	2.875	2.0	43.25	52.25	34.25	2	¾ x 2½	8.00
76.1 mm	3.000	2.0	+	+	+	2	10 x 63	+
3	3.500	2.4	50.00	61.50	39.25	2	¾ x 2½	8.00
108.0 mm	4.250	4.8	+	+	+	2	10 x 63	+
4	4.500	3.8	70.50	84.75	52.50	2	¾ x 2½	8.00
133.0 mm	5.250	4.5	+	+	+	2	12 x 70	+
139.7 mm	5.500	4.8	+	+	+	2	12 x 70	+
5	5.563	4.5	88.25	111.50	53.00	2	½ x 3	10.25
159.0 mm	6.250	5.5	+	+	+	2	12 x 70	+
165.1 mm	6.500	5.4	+	+	+	2	12 x 70	+
6	6.625	5.5	106.25	129.00	58.25	2	½ x 3	10.25
8	8.625	11.4	177.50	216.00	83.75	2	¾ x 4¼	12.25

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Note: Style 005 FireLock bolts and nuts are sized for use with Style 005 couplings only and must not be used with other Victaulic products.


Grade E (Type A) EPDM gaskets are applicable for wet and dry fire sprinkler systems (ambient temperature) only.

† Coupling less gasket is additional. Contact Victaulic for details.

FireLock Rigid Coupling

STYLE 005
Request publication 10.02



  
Rubber Gasketed
Pipe Fittings 913H
Request Victaulic
publication 10.01 for details.

STYLE 005 – VIC-PLUS GRADE “E” FLUSHSEAL GASKET

PIPE Inches	Aprx. Wgt. Each (lbs)	COUPLING COMPLETE † With Vic-Plus § Grade “E” (Type A) Gasket		SPARE PARTS Grade “E” Vic-Plus FlushSeal Gasket Only Price Each
		Price Each		
Nom. Size		Painted	Galvanized	
1¼	1.5	\$43.75	\$49.00	\$37.00
1½	1.6	46.25	53.75	41.25
2	1.9	49.75	58.00	44.75
2½	2.0	59.25	68.75	46.75
3	2.4	64.00	74.75	55.25
4	3.8	90.00	104.75	74.00
5	4.5	152.25	176.00	106.00
6	5.5	168.50	196.75	136.00
8	11.4	273.00	316.50	149.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

† Coupling less gasket is additional. Contact Victaulic for details.

Standard gasket and FlushSeal gasket approved for dry pipe systems down to -40°F. For dry services, Victaulic continues to recommend the use of FlushSeal gaskets.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

For complete contact information, visit www.victaulic.com

PL2008-C-FP-ADD6 5953 REV A

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

PL2008-C-FP-ADD6

