

# Victaulic Bolted Split-Sleeve Couplings Quote Check Sheet



Send inquires to: [projectcoordination@victaulic.com](mailto:projectcoordination@victaulic.com) or fax to: 610-923-3477  
 To speak with a Customer Service representative in the US, please call 1-800-PICK-VIC  
 In Canada, please email [vcoc\\_spr@victaulic.com](mailto:vcoc_spr@victaulic.com) or fax 905-884-9774

**TO OBTAIN A QUOTE, PLEASE PROVIDE THE INFORMATION REQUESTED BELOW:**

## CUSTOMER CONTACT INFORMATION:

NAME:	DATE:
COMPANY:	PHONE:
ADDRESS:	FAX:
CITY, STATE, ZIP:	E-MAIL:

## PROJECT INFORMATION:

PROJECT NAME:	QUOTE NEEDED BY (date):
CITY & STATE:	BID DATE:
PROJECT SPEC. INCLUDED	REQUESTED SHIPPING DATE:
ENGINEERING FIRM:	CONTACT NAME:
CITY & STATE:	PHONE:

## PROJECT REQUIREMENTS:

Domestic Only    Legislative Act:	Material Traceability
Material Certifications	

## APPLICATION DATA:

PIPE MATERIAL:			
CARBON STEEL	STAINLESS STEEL	DUCTILE IRON	CAST IRON
CONCRETE (RCCP/CPP)	FIBERGLASS (FRP/GRP)	HDPE (SDR:     /     ID)	OTHER:

SERVICE DATA:			
SERVICE TYPE:	Air	Water	Wastewater    Other:
SERVICE PRESSURE:	Working Pressure:	Test Pressure:	Surge Pressure:
SERVICE TEMPERATURE	MIN. °F/°C:	Max. °F/°C:	

# Victaulic Bolted Split-Sleeve Couplings Quote Check Sheet



**NOTE:** Please fill out the information below completely as possible to ensure receiving the most accurate quote and to expedite the process.

## PRODUCTS AVAILABLE FOR QUOTE:

Style 230/230S Non-Restrained Coupling	Style 231/231S Expansion Coupling	Style 232/232S Restrained Coupling
Style 233/233S Restrained Coupling for Joint Deflection	Style 234/234S Restrained Single Gasket Coupling	Style 229S Non-Restrained Coupling

## COUPLING DATA:

QTY	ACTUAL PIPE OD	COUPLING STYLE #	# OF HOUSING SEGMENTS	AXIAL MOVEMENT REQUIRED (Style 231/231S only)	COMMENTS

## COUPLING DETAIL REQUIREMENTS:

O-RING/GASKET MATERIAL:	Standard:	EDPM	Silicone	Isoprene
	Optional:	Nitrile	Fluoroelastomer (Viton <sup>*</sup> )	Neoprene
		Split for field bonding (not available for Silicone)	Built-In (limited availability/contact Victaulic)	Other:
HARDWARE:	Carbon Steel (Zinc Plated)	Stainless Steel (Type 316)	Other:	
LINING/COATING:	Tnemec 140-1211 Liquid Epoxy	Corvel 10-7208 Fusion Bonded Epoxy	Other:	
	Water Based Enamel, Orange	Unfinished		

## COUPLING OPTIONS:

STYLE 230/230S ADD-ONS:	Pipe Stops	Insulating Sleeves	Sleeve Material (EPDM Standard):
-------------------------	------------	--------------------	----------------------------------

## INSTALLATION TOOLS:

MANUAL:	CTM-01 (small manual closure tool) QTY:	CTM-02 (large manual closure tool) QTY:
HYDRAULIC:	CTH-01 (10-ton hydraulic closure tool) QTY:	CTH-02 (25-ton hydraulic closure tool) QTY:

## SPARE/REPLACEMENT COMPONENTS (must provide coupling data above of previous order # for reference):

HARDWARE SET (B/N/W):	Carbon Steel (Zinc Plated)	Stainless Steel (Type 316)	Other:
RESTRAINT RING:	Carbon Steel (ASTM A108 1018)	Stainless Steel (ASTM A240 316)	Other:
O-RING/GASKET:	Material:	Split for field bonding (not available for Silicone)	
SEALING PLATE:	Pad Material:		

**NOTE:** Replacement components may require additional details about the coupling(s). To ensure that replacement parts will fit your product application, your previous purchase order number or a Victaulic customer order number may be helpful in determining the correct size/materials of components. Please contact Victaulic for assistance.

\*Viton is a registered trademark of Dupont