

Price List Addendum

EFFECTIVE October 16, 2019



PL2019-GEN-ADD10

QuickVic™ Installation-Ready™ Couplings for Stainless Steel/Galvanized Carbon Steel Pipe in Potable Water Applications

QuickVic™
Installation-Ready™
Rigid Coupling for
Stainless Steel/
Galvanized Carbon
Steel Pipe in Potable
Water Applications

STYLE 807N

Refer to publication 06.28



STYLE 807N – GRADE “P” GASKET

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE With Grade “P” Gasket		SPARE PARTS
inches			Price Each		
Nom. Size	Outside Dia.	lb	Painted	Galv.	Grade “P” Gasket
2	2.375	2.7	\$102.50	\$129.00	\$80.50
2½	2.875	3.0	117.00	146.50	87.00
3	3.500	3.7	134.50	171.50	99.00
4	4.500	5.1	187.00	241.00	132.00
6	6.625	8.2	315.50	410.00	220.00
8	8.625	15.1	498.00	647.50	264.50
10	10.750	23.6	964.50	1286.50	306.00
12	12.750	27.2	1077.50	1443.00	339.50

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

QuickVic™
Installation-Ready™
Flexible Coupling
for Stainless Steel/
Galvanized Carbon
Steel Pipe in Potable
Water Applications

STYLE 877N

Refer to publication 06.29



STYLE 877N – GRADE “P” GASKET

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE With Grade “P” Gasket		SPARE PARTS
inches			Price Each		
Nom. Size	Outside Dia.	lb	Painted	Galv.	Grade “P” Gasket
2	2.375	3.3	\$103.00	\$135.00	\$80.50
2½	2.875	3.8	119.50	166.00	87.00
3	3.500	4.3	132.00	182.00	99.00
4	4.500	7.4	190.50	267.50	132.00
6	6.625	12.8	338.50	483.50	220.00
8	8.625	20.7	581.50	863.00	264.50

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.



Products for Copper Tubing in Potable Water Applications

QuickVic™ Rigid Coupling for Copper Tubing

STYLE 607

Refer to publication 22.13



STYLE 607 – GRADE “P” GASKET

PIPE inches	Approx. Weight Each	COUPLING COMPLETE With Grade “P” Gasket	SPARE PARTS
Nominal Size	lb	Price Each	Grade “P” Gasket
2	1.9	\$84.00	\$69.00
2½	2.1	93.50	75.00
3	3.0	105.00	78.50
4	3.3	157.50	113.50
5	5.5	262.50	186.00
6	5.8	347.00	245.00
8	7.7	536.00	379.50

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Installation-Ready™ Transition Coupling for Copper Tubing to Stainless Steel Pipe in Potable Water Applications

STYLE 644

Refer to publication 22.44



STYLE 644 – GRADE “P” GASKET

Nominal Size inches	Actual Outside Diameter		Approx. Weight Each lb	COUPLING COMPLETE With Grade “P” Gasket Price Each	SPARE PARTS Grade “P” Gasket
	Stainless Steel Pipe inches	Copper Tubing inches			
2	2.375	2.125	2.4	\$125.50	\$69.00
2½	2.875	2.625	2.6	140.50	75.00
3	3.500	3.125	3.5	157.50	78.50
4	4.500	4.125	4.2	236.00	113.50
6	6.625	6.125	7.2	519.00	245.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Products for Use in Potable Water Applications

Mechanical-T Cross Assembly for Copper Tubing in Potable Water Applications

STYLE 622

Refer to publication 22.12



STYLE 622 – GRADE “P” GASKET

Run x Branch	Approx. Weight Each	COMPLETE <i>MECHANICAL-T</i> With Grade “P” Gasket
Nominal Size inches	lb	Price Each
2½ x ¾	3.1	\$313.50
	3.2	358.50
	4.1	440.50
3 x ¾	3.4	348.50
	3.6	373.00
	4.5	463.00
4 x ¾	3.3	393.50
	4.0	415.50
	5.0	502.50

Mechanical-T Bolted Branch Outlet for Copper Tubing in Potable Water Applications

STYLE 622 CROSS

Refer to publication 22.12



STYLE 622 CROSS – GRADE “P” GASKET

Run x Branch	Approx. Weight Each	COMPLETE <i>MECHANICAL-T</i> Cross With Grade “P” Gasket
Nominal Size inches	lb	Price Each
2½ x ¾	4.2	\$571.50
	4.4	678.00
	6.2	870.50
3 x ¾	4.4	606.50
	4.8	702.00
	6.6	914.50
4 x ¾	4.5	737.00
	5.4	782.50
	7.4	970.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Couplings for CPVC/PVC Pipe in Potable Water Applications

Installation-Ready™
Transition Coupling
for CPVC/PVC Pipe
in Potable Water
Applications

STYLE 856

CPVC/PVC to Steel
Refer to publication 33.16



STYLE 856 – GRADE “P” GASKET

PIPE inches		Approx. Wgt. Ea. lb	COUPLING COMPLETE With Grade “P” Gasket	SPARE PARTS	
Nom. Size	Outside Dia.		Price Each	Plated Bolt & Nut	
			Painted	No.	Size inches
2	2.375	2.6	\$60.50	2	3/8 x 2 1/2
2 1/2	2.875	3.5	68.50	2	3/8 x 2 1/2
3	3.500	4.3	76.00	2	1/2 x 3
4	4.500	5.9	107.00	2	1/2 x 3 1/4
6	6.625	8.1	181.50	2	1/2 x 3 1/4
8	8.625	17.6	289.00	2	3/4 x 5
10	10.750	22.8	525.00	2	3/4 x 6 1/4
12	12.750	24.9	637.00	2	3/4 x 6 1/4

NOTE: See Spare Parts Section in PL2019-GEN for spare bolt and nut prices.

NOTE: The Style 856 transition coupling uses the Style 807N gasket.

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

Installation-Ready™
Rigid Coupling for
CPVC/PVC Pipe
in Potable Water
Applications

STYLE 857

Refer to publication 33.17



STYLE 857 – GRADE “P” GASKET

PIPE inches		Approx. Wgt. Ea. lb	COUPLING COMPLETE With Grade “P” Gasket	SPARE PARTS	
Nom. Size	Outside Dia.		Price Each	Plated Bolt & Nut	
			Painted	No.	Size inches
2	2.375	3.3	\$57.00	2	3/8 x 2 1/2
2 1/2	2.875	3.6	64.50	2	3/8 x 2 1/2
3	3.500	4.4	73.00	2	1/2 x 3
4	4.500	6.1	103.00	2	1/2 x 3 1/4
6	6.625	8.8	173.00	2	1/2 x 3 1/4
8	8.625	18.1	274.00	2	3/4 x 5
10	10.750	23.5	499.50	2	3/4 x 6 1/4
12	12.750	25.6	599.50	2	3/4 x 6 1/4

NOTE: See Spare Parts Section in PL2019-GEN for spare bolt and nut prices.

NOTE: The Style 857 rigid coupling uses the Style 807N gasket.

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com