

Roll Grooving Tools – Field Fabrication

RG3212



The RG3212 is a self-contained, transportable roll grooving tool with an integral drive motor and hydraulic feed unit. The RG3212 requires a 120V, 15 -amp power source. The tool is supplied with a PS3212 pipe stand and roll sets for 2"-12" carbon steel pipe.

Tool Model	Part Number	Tool Weight lb	Tool List Price
RG3212 Roll Grooving Tool with PS3212 Pipe Stand	R0003212RG	302	\$10190.00

For tool rating capacity please reference publication 24.19.

RG3212 GROOVING ROLLS *

Pipe Material	Part Number	Pipe Size Range inches I DN	Purchase List Price Each Set †
Standard	R902321203	2 – 3½/50 – 90	\$1896.00
	R904321206	4 – 6/100 – 150	2026.00
	R908321212	8 – 12/200 – 300	2259.00

† Upper and lower rolls (1 of each per set) can be sold separately. Contact Victaulic.

* Refer to How to Order in PL2019-GEN.

NOTE: Roll sets for the RG3212 are not compatible with other roll grooving tools.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Please reference submittal publication 24.19 when referencing wall thickness and tool capacity ratings.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com