

Grooved Carbon Steel Pipe Couplings

Carbon Steel Rigid Coupling

STYLE L07

SA352 Grade LCC
Refer to publication 51.01



STYLE L07 – GRADE “E” OR “T” GASKET, TYPE 316 STAINLESS STEEL HARDWARE

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE With Grade “E” or “T” Gasket		COUPLING COMPLETE With Grade “L” Gasket	
inches			Price Each		Price Each	
Nom. Size	Outside Dia.	lb	Painted	Galv.	Painted	Galv.
1½	1.900	1.8	\$310.00	\$343.00	+	+
2	2.375	2.5	374.00	415.00	+	+
2½	2.875	2.9	389.00	432.00	+	+
3	3.500	3.3	392.00	436.00	+	+
4	4.500	5.8	465.00	520.00	+	+
6	6.625	9.1	595.00	671.00	+	+
8	8.625	16.6	882.00	1002.00	+	+
10	10.750	25.9	1311.00	1491.00	+	+
12	12.750	31.0	1392.00	1591.00	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

AGS[™] Carbon Steel Rigid Coupling

AGS STYLE LW07

Refer to publication 51.01



AGS STYLE LW07 – GRADE “E” OR “T” GASKET, TYPE 316 STAINLESS STEEL HARDWARE

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE With Grade “E” or “T” Gasket		COUPLING COMPLETE With Grade “L” Gasket	
inches			Price Each		Price Each	
Nom. Size	Outside Dia.	lb	Painted	Galv.	Painted	Galv.
14	14.000	59.0	+	+	+	+
16	16.000	72.0	+	+	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon Steel Flexible Coupling

STYLE L77

SA352 Grade LCC
Refer to publication 51.01



STYLE L77 – GRADE “E” OR “T” GASKET, TYPE 316 STAINLESS STEEL HARDWARE

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE With Grade “E” or “T” Gasket		COUPLING COMPLETE With Grade “L” Gasket	
inches			Price Each		Price Each	
Nom. Size	Outside Dia.	lb	Painted	Galv.	Painted	Galv.
1½	1.900	2.3	\$310.00	\$343.00	+	+
2	2.375	2.9	374.00	415.00	+	+
2½	2.875	3.4	389.00	432.00	+	+
3	3.500	4.1	392.00	436.00	+	+
4	4.500	7.4	465.00	520.00	+	+
6	6.625	13.3	595.00	671.00	+	+
8	8.625	23.1	882.00	1002.00	+	+
10	10.750	30.9	1311.00	1491.00	+	+
12	12.750	34.5	1392.00	1591.00	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Grooved Carbon Steel Pipe Fittings

Carbon Steel Long Radius Elbows

SA352 Grade LCC
Refer to publication 51.01



No. L100



No. L110

CARBON STEEL – 90° LONG RADIUS ELBOW NO. L100 OR 45° LONG RADIUS ELBOW NO. L110

Nom. Size inches	90° Long Radius Elbow No. L100			45° Long Radius Elbow No. L110		
	Approx. Wgt. Ea. lb	Price Each		Approx. Wgt. Ea. lb	Price Each	
		Painted	Galv.		Painted	Galv.
1½ †	1.8	\$215.00	\$247.50	1.3	\$215.00	\$247.50
2 †	3.6	280.00	322.00	2.1	280.00	322.00
2½ †	6.9	345.00	397.00	4.0	345.00	397.00
3 †	8.2	393.00	473.00	5.8	393.00	452.00
4	12.0	500.00	575.00	7.7	500.00	575.00
6	31.0	1357.00	1561.00	18.0	1357.00	1600.00
8	65.0	2939.00	3380.00	49.0	2939.00	3501.00
10 *	130.0	+	+	78.0	+	+
12 *	192.0	+	+	95.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

† Schedule 80 wall thickness. For other wall thickness options, contact Victaulic.

* ASTM A420 WPL6 wrought fitting with A333 Grade 6 tangents. Contact Victaulic for cast options.

AGS Carbon Steel AGS Long Radius Elbows

SA352 Grade LCC
Refer to publication 51.01



No. LW100



No. LW110

CARBON STEEL AGS LONG RADIUS – 90° LONG RADIUS ELBOW OR 45° LONG RADIUS ELBOW

Nom. Size inches	90° Long Radius Elbow No. LW100			45° Long Radius Elbow No. LW110		
	Approx. Wgt. Ea. lb	Price Each		Approx. Wgt. Ea. lb	Price Each	
		Painted	Galv.		Painted	Galv.
14	273.0	+	+	144.0	+	+
16	366.0	+	+	208.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

Carbon Steel Tee

SA352 Grade LCC
Refer to publication 51.01



No. L20

NO. L20 TEE – CARBON STEEL

Nom. Size	Approx. Wgt. Ea.	Tee No. L20	
		Price Each	
inches	lb	Painted	Galv.
1½ †	2.4	\$220.00	\$253.00
2 †	3.7	290.00	333.50
2½ †	6.6	360.00	414.00
3 †	9.2	415.00	477.50
4	11.7	550.00	632.50
6	35.9	1500.00	1725.00
8	65.6	3200.00	3680.00
10 *	136.0	+	+
12 *	151.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.
Carbon steel wall thickness is standard weight unless otherwise noted.
Fittings are cast unless otherwise noted.

† Schedule 80 wall thickness. For other wall thickness options, contact Victaulic.

* ASTM A420 WPL6 wrought fitting with A333 Grade 6 tangents. Contact Victaulic for cast options.

AGS™ AGS Carbon Steel Tee

SA352 Grade LCC
Refer to publication 51.01



No. LW20

NO. LW20 AGS CARBON STEEL TEE

Nom. Size	Approx. Wgt. Ea.	Tee No. LW20	
		Price Each	
inches	lb	Painted	Galv.
14	170.0	+	+
16	278.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.
Carbon steel wall thickness is standard weight unless otherwise noted.
Fittings are cast unless otherwise noted.

Carbon Steel Reducing Tee

SA352 Grade LCC
Refer to publication 51.01



No. L25

NO. L25 CARBON STEEL REDUCING TEE

Size				Approx. Wgt. Each lb	Reducing Tee No. L25	
inches					Price Each	
Run x Branch					Painted	Galv.
2	x	2	x 1½ †	3.1	\$400.00	\$460.00
3	x	3	x 1½ †	7.9	431.00	516.00
			2 †	8.1	453.00	541.00
4	x	4	x 1½ †	12.9	805.00	957.00
			2 †	13.0	816.00	971.00
			2½ †	16.9	962.00	1150.00
			3 †	14.3	891.00	1060.00
6	x	6	x 2 †	33.6	2282.00	2625.00
			3 †	35.5	2305.00	2650.00
			4	34.5	2400.00	2760.00
8	x	8	x 2 †	60.9	3200.00	3680.00
			2½ †	66.0	3200.00	3680.00
			3 †	66.0	3300.00	3795.00
			4	60.5	3515.00	4042.50
			6	62.3	3515.00	4042.50
10	x	10	x 6	96.7	5125.00	5894.00
			8	100.3	5125.00	5894.00
12	x	12	x 8*	172.0	+	+
			10*	182.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

† Schedule 80 wall thickness. For other wall thickness options, contact Victaulic.

* ASTM A420 WPL6 wrought fitting with A333 Grade 6 tangents. Contact Victaulic for cast options.

AGS AGS Carbon Steel Reducing Tee

SA352 Grade LCC
Refer to publication 51.01



No. LW25

NO. LW25 AGS CARBON STEEL REDUCING TEE

Size				Approx. Wgt. Each lb	Reducing Tee No. LW25	
inches					Price Each	
Run x Branch					Painted	Galv.
14	x	14	x 4	210.0	+	+
			8	205.0	+	+
			10	200.0	+	+
16	x	16	x 4	234.0	+	+
			6	238.0	+	+
			8	248.0	+	+
			10	262.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

Victaulic® Carbon Steel Couplings and Grooved Fittings

Carbon Steel Reducers

SA352 Grade LCC
Refer to publication 51.01



No. L50



No. L51

CARBON STEEL REDUCERS – CONCENTRIC OR ECCENTRIC

Size		Concentric Reducer No. L50			Eccentric Reducer No. L51		
inches		Approx. Wgt. Ea. lb	Price Each		Approx. Wgt. Ea. lb	Price Each	
			Painted	Galv.		Painted	Galv.
2	x 1½ †	1.3	\$145.00	\$167.00	1.0	\$150.00	\$172.50
3	x 1½ †	2.2	145.00	167.00	2.2	340.00	391.00
	2 †	2.2	145.00	167.00	2.9	340.00	391.00
4	x 1½ †	3.9	274.00	315.50	4.2	450.00	517.50
	2 †	3.5	274.00	315.50	3.4	450.00	517.50
	2½ †	4.6	274.00	315.50	–	–	–
	3 †	4.4	274.00	315.50	4.1	450.00	517.50
6	x 2 †	7.8	510.00	587.00	8.8	768.00	883.50
	3 †	9.9	600.00	690.00	9.1	768.00	883.50
	4	7.3	650.00	748.00	10.3	768.00	883.50
8	x 4	15.7	870.00	1000.00	11.7	959.00	1103.00
	6	17.9	966.00	1111.00	12.7	959.00	1103.00
10	x 4	24.0	1600.00	1840.00	–	–	–
	6	26.9	1700.00	1955.00	19.1	1705.00	1961.00
	8	29.2	1700.00	1955.00	19.8	1705.00	1961.00
12	x 8	39.2	2950.00	3392.50	40.2	2998.00	3448.00
	10	43.5	2950.00	3392.50	31.7	2998.00	3448.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

† Schedule 80 wall thickness. For other wall thickness options, contact Victaulic.

AGS™ AGS Carbon Steel Reducers

SA352 Grade LCC
Refer to publication 51.01



No. LW50



No. LW51

AGS CARBON STEEL REDUCERS – CONCENTRIC OR ECCENTRIC

Size		Concentric Reducer No. LW50			Eccentric Reducer No. LW51		
inches		Approx. Wgt. Ea. lb	Price Each		Approx. Wgt. Ea. lb	Price Each	
			Painted	Galv.		Painted	Galv.
14	x 8	90.0	+	+	100.0	+	+
	10	96.0	+	+	–	–	–
	12	105.0	+	+	124.0	+	+
16	x 8	104.0	+	+	132.0	+	+
	10	108.0	+	+	138.0	+	+
	12	112.0	+	+	–	–	–

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

Victaulic® Carbon Steel Couplings and Grooved Fittings

Carbon Steel Reducer – Female Threaded

SA352 Grade LCC
Refer to publication 51.01



No. L52

CARBON STEEL REDUCER – FEMALE THREADED

Size		Reducer – Female Threaded No. L52		
inches	Run x Branch	Approx. Wgt. Each lb	Price Each	
			Painted	Galv.
1½	x ¾ †	1.0	\$160.00	\$184.00
	1 †	1.0	160.00	184.00
2	x ¾ †	1.4	171.00	197.00
	1 †	1.3	171.00	197.00
	1½ †	1.3	171.00	197.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

† Schedule 80 wall thickness. For other wall thickness options, contact Victaulic.

Carbon Steel Cap

SA352 Grade LCC
Refer to publication 51.01



No. L60

CARBON STEEL CAP

Nominal Size	Cap No. L60		
inches	Approx. Wgt. Ea.	Price Each	
	lb	Painted	Galv.
1½	0.5	\$122.00	\$140.50
2	0.8	122.00	140.50
3	1.8	122.00	140.50
4	3.7	197.00	236.00
6	8.3	464.00	555.00
8	15.8	916.00	1094.00
10	28.0	+	+
12	41.6	2387.00	2851.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

AGS Carbon Steel Cap

SA352 Grade LCC
Refer to publication 51.01



No. LW60

AGS CARBON STEEL CAP

Nominal Size	AGS Cap No. LW60		
inches	Approx. Wgt. Ea.	Price Each	
	lb	Painted	Galv.
14	33.2	+	+
16	41.2	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Carbon steel wall thickness is standard weight unless otherwise noted.

Fittings are cast unless otherwise noted.

Victaulic® Carbon Steel Couplings and Grooved Fittings

Carbon Steel Flanged Adapter Nipples

SA352 Grade LCC
Refer to publication 51.01



No. L45R



No. L46R

FLANGED ADAPTER NIPPLES – 150 LB OR 300 LB *

Size x Length	150# Flanged Adapter Nipple No. L45R Raised Face			300# Flanged Adapter Nipple No. L46R Raised Face		
	Approx. Wgt. Ea.	Price Each		Approx. Wgt. Ea.	Price Each	
		lb	Painted		Galv.	lb
1½ x 4	3.7	\$490.00	\$563.50	6.5	\$550.00	\$632.50
2 x 4	6.8	510.00	586.50	8.0	630.00	724.50
2½ x 4	10.1	625.00	719.00	-	-	-
3 x 4	11.7	725.00	834.00	15.8	825.00	949.00
4 x 6	16.4	780.00	897.00	28.4	1046.00	1238.00
6 x 6	26.0	1200.00	1380.00	42.2	1600.00	1840.00
8 x 6	39.6	1554.00	1832.00	64.6	2430.00	2871.00
10 x 8	61.6	2540.00	2985.00	103.0	+	+
12 x 8	85.8	3833.00	4484.00	133.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

AGS® Carbon Steel AGS Flanged Adapter Nipple

SA352 Grade LCC
Refer to publication 51.01



No. LW45R

NO. LW45R CARBON STEEL AGS FLANGED ADAPTER NIPPLE

Size x Length	150# Flanged Adapter Nipple No. LW45R Raised Face		
	Approx. Wgt. Ea.	Price Each	
		lb	Painted
14 x 8	128.0	+	+
16 x 8	149.0	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

**Carbon Steel
Mechanical-T Outlet**

STYLE L920N

SA352 Grade LCC
Refer to publication 51.01



Style L920N – Female Threaded

STYLE L920N – FEMALE THREADED BRANCH, TYPE 316 STAINLESS STEEL HARDWARE

Size		MECHANICAL-T Outlet – Style L920N		
inches Run x Branch	Approx. Wgt. Ea. lb	Price Each		
		Painted	Galv.	
2 x 1/2	3.3	\$410.00	\$456.00	
	3.1	413.00	458.00	
	3.0	418.00	463.00	
3 x 3/4	3.4	421.00	468.00	
	3.3	426.00	473.00	
4 x 1/2	3.7	426.00	475.00	
	3.7	427.00	476.00	
	3.7	433.00	481.00	
6 x 3/4	5.1	500.00	557.00	
	5.7	515.00	576.00	
	6.5	515.00	576.00	
8 x 3/4	11.6	792.00	890.00	
	11.3	824.00	927.00	
10 x 3/4	16.5	891.00	1011.00	
	15.2	914.00	1033.00	
12 x 3/4	19.4	1049.00	1189.00	
	20.5	1064.00	1209.00	
14 x 3/4	24.2	1365.50	1546.50	
	24.2	1384.00	1566.50	
16 x 3/4	26.6	1442.50	1636.00	

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com