

Price List Addendum

EFFECTIVE June 13, 2019



PL2019-GEN-ADD3

Couplings for HDPE Pipe

Coupling for Plain End HDPE Pipe

STYLE 905

Refer to publication 19.07



STYLE 905 IPS STANDARD – GRADE “E” OR “T” GASKET, STANDARD OR FLUSH-SEAL™

| PIPE inches | | Approx. Weight Each lb | COUPLING COMPLETE With Grade “E” or “T” Gasket | | COUPLING COMPLETE With Grade “E” or “T” Flush-Seal Gasket | | Grade “E” or “T” Gasket Only Price Each | Grade “E” or “T” Flush-Seal Gasket Only Price Each | Fluoropolymer Coated Bolt/Nut/Washer § | | | Stainless Steel Retaining Ring † Price Each |
|--------------|------------------|---------------------------|--|----------|---|----------|--|---|--|-------------|------------|--|
| Nominal Size | Outside Diameter | | Painted * | Coated * | Painted * | Coated * | | | No. | Size inches | Price Each | |
| 2 | 2.375 | 5.5 | \$182.50 | \$365.00 | \$201.00 | \$402.00 | \$59.50 | \$78.00 | 2 | 1/2 x 3/4 | \$22.00 | \$55.00 |
| 3 | 3.500 | 8.5 | 222.50 | 445.00 | 244.50 | 489.00 | 62.00 | 84.50 | 2 | 5/8 x 3/2 | 32.50 | 86.50 |
| 4 | 4.500 | 13.1 | 282.50 | 565.00 | 310.50 | 621.00 | 103.50 | 132.00 | 2 | 5/8 x 4/4 | 36.50 | 116.50 |
| 5 | 5.563 | 18.7 | 415.50 | 831.00 | – | – | 120.50 | – | 2 | 3/4 x 4/4 | 56.00 | 146.00 |
| 6 | 6.625 | 19.4 | 451.50 | 903.00 | 496.50 | 993.00 | 130.50 | 176.00 | 2 | 3/4 x 5 | 69.50 | 173.50 |
| 8 | 8.625 | 25.0 | 599.00 | 1198.00 | 659.00 | 1318.00 | 172.00 | 232.50 | 4 | 3/4 x 6/4 | 74.50 | 226.00 |
| 10 | 10.750 | 73.5 | 729.00 | 1458.00 | – | – | 225.00 | – | 4 | 7/8 x 6/2 | 101.50 | 282.50 |
| 12 | 12.750 | 86.5 | 807.50 | 1615.00 | – | – | 250.00 | – | 4 | 7/8 x 6/2 | 101.50 | 339.00 |
| 14 | 14.000 | 112.6 | 1462.50 | 2925.00 | – | – | 424.50 | – | 4 | 1 1/8 x 7 | 125.00 | 395.50 |

STYLE 905 ISO STANDARD – GRADE “E” OR “T” GASKET

| ISO Size | Approx. Weight Each | Wgt. Each | COUPLING COMPLETE With Grade “E” or “T” Gasket | | Grade “E” or “T” Gasket Only Price Each | Fluoropolymer Coated Bolt/Nut/Washer § | | | Stainless Steel Retaining Ring † Price Each |
|-----------|---------------------|-----------|--|-----------|--|--|-----------|-------------|--|
| O.D. [mm] | lb | | [kg] | Painted * | | Coated * | No. | Size inches | |
| 63 | 5.5 | 2.5 | \$182.50 | \$365.00 | \$59.50 | 2 | 1/2 x 3/4 | \$22.00 | \$55.00 |
| 75 | 8.1 | 3.7 | 198.00 | 396.00 | 60.50 | 2 | 5/8 x 3/2 | 32.50 | 68.50 |
| 90 | 8.5 | 3.9 | 222.50 | 445.00 | 62.00 | 2 | 5/8 x 4 | 32.50 | 86.50 |
| 110 | 13.0 | 5.9 | 282.50 | 565.00 | 103.50 | 2 | 5/8 x 4 | 36.50 | 117.00 |
| 125 | 17.3 | 7.8 | 316.50 | 633.00 | 111.00 | 2 | 3/4 x 4/4 | 56.00 | 125.00 |
| 140 | 18.7 | 8.5 | 415.50 | 831.00 | 120.50 | 2 | 3/4 x 4/4 | 56.00 | 146.00 |
| 160 | 19.3 | 8.8 | 451.50 | 903.00 | 130.50 | 2 | 3/4 x 5 | 69.50 | 173.50 |
| 180 | 25.4 | 11.5 | 508.00 | 1016.00 | 148.00 | 4 | 3/4 x 6/4 | 69.50 | 186.50 |
| 200 | 26.8 | 12.2 | 599.00 | 1198.00 | 166.00 | 4 | 3/4 x 6/4 | 74.50 | 203.50 |
| 225 | 28.7 | 13.0 | 610.00 | 1220.00 | 178.50 | 4 | 3/4 x 6/4 | 74.50 | 237.50 |
| 250 | 73.5 | 30.9 | 729.00 | 1458.00 | 225.00 | 4 | 7/8 x 6/2 | 101.50 | 282.50 |
| 280 | 78.0 | 35.4 | 768.50 | 1537.00 | 237.50 | 4 | 7/8 x 6/2 | 101.50 | 311.00 |
| 315 | 83.9 | 38.1 | 807.50 | 1615.00 | 250.00 | 4 | 7/8 x 6/2 | 101.50 | 339.00 |
| 355 | 112.6 | 51.1 | 1462.50 | 2925.00 | 424.50 | 4 | 1 1/8 x 7 | 125.00 | 395.50 |

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

§ Price includes one bolt, nut, and washer for coupling sizes 2" - 4" | 63mm - 160mm and one bolt, nut, and two washers for coupling sizes 5" - 14" | 180mm - 355mm.

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

† Set of two required for coupling sizes through 2" - 8" | 63mm - 225mm. Set of four required for coupling sizes through 10" - 14" | 250mm - 355mm.

* “Painted” option includes enamel coating with fluoropolymer-coated hardware. “Coated” option includes liquid bonded epoxy coating with stainless steel hardware.

NOTE: Fusion bonded epoxy and galvanized finishes available. Contact Victaulic for pricing.



Couplings for HDPE Pipe

Transition Coupling for HDPE-to-Steel Pipe

STYLE 907

Refer to publication 19.10



STYLE 907 & STYLE W907 IPS STANDARD – GRADE “E” OR “T” GASKET

| PIPE inches | | Style Number | Approx. Weight Each | COUPLING COMPLETE With Grade “E” or “T” Gasket | | Grade “E” or “T” Gasket Only | Fluoropolymer Coated Bolt/Nut/Washer § | | | Stainless Steel Retaining Ring † |
|--------------|------------------|--------------|---------------------|--|----------|------------------------------|--|--------|-------------|----------------------------------|
| Nominal Size | Outside Diameter | | | Price Each | | | Price Each | No. | Size inches | |
| | | | lb | Painted * | Coated * | | | | | |
| 2 | 2.375 | 907 | 4.7 | \$231.00 | \$462.00 | \$59.50 | 2 | ½ x ¾ | \$22.00 | \$55.00 |
| 3 | 3.500 | | 6.6 | 274.50 | 549.00 | 62.00 | 2 | ⅝ x ¾ | 32.50 | 86.50 |
| 4 | 4.500 | | 9.4 | 341.00 | 682.00 | 103.50 | 2 | ⅝ x 4¼ | 36.50 | 116.50 |
| 5 | 5.563 | | 11.9 | 479.50 | 959.00 | 120.50 | 2 | ¾ x 4¼ | 56.00 | 146.00 |
| 6 | 6.625 | | 13.8 | 516.00 | 1032.00 | 130.50 | 2 | ¾ x 5 | 69.50 | 173.50 |
| 8 | 8.625 | | 21.4 | 689.00 | 1378.00 | 172.00 | 2 | ¾ x 6¼ | 74.50 | 226.00 |
| 10 | 10.750 | | 53.0 | 911.00 | 1822.00 | 225.00 | 4 | ⅞ x 6½ | 101.50 | 282.50 |
| 12 | 12.750 | | 62.0 | 1009.00 | 2018.00 | 250.00 | 4 | ⅞ x 6½ | 101.50 | 339.00 |
| 14 | 14.000 | W907 | 81.0 | 1828.50 | 3657.00 | 424.50 | 4 | 1½ x 7 | 125.00 | 395.50 |

STYLE 907 & W907 ISO STANDARD – GRADE “E” OR “T” GASKET

| ISO Size | Nominal Size HDPE Plain End x Actual Size Grooved End | Style Number | Approx. Weight Each | Wgt. Each | COUPLING COMPLETE With Grade “E” or “T” Gasket | | Grade “E” or “T” Gasket Only | Fluoropolymer Coated Bolt/Nut/Washer § | | | Stainless Steel Retaining Ring † |
|-------------|---|--------------|---------------------|-----------|--|----------|------------------------------|--|--------|-------------|----------------------------------|
| | | | | | Price Each | | | Price Each | No. | Size inches | |
| | | | lb | [kg] | Painted * | Coated * | | | | | |
| 63 x 60.3 | | 907 | 4.9 | 2.2 | \$231.00 | \$462.00 | \$59.50 | 2 | ½ x ¾ | \$22.00 | \$55.00 |
| 75 x 73.0 | | | 5.9 | 2.7 | 243.00 | 486.00 | 60.50 | 2 | ⅝ x ¾ | 32.50 | 68.50 |
| 90 x 88.9 | | | 6.5 | 3.0 | 274.50 | 549.00 | 62.00 | 2 | ⅝ x 4 | 36.50 | 86.50 |
| 110 x 114.3 | | | 9.6 | 4.4 | 341.00 | 682.00 | 103.50 | 2 | ⅝ x 4 | 36.50 | 117.00 |
| 125 x 114.3 | | | 11.3 | 5.1 | 379.50 | 759.00 | 111.00 | 2 | ¾ x 4¼ | 56.00 | 125.00 |
| 140 x 141.3 | | | 11.9 | 5.4 | 479.50 | 959.00 | 120.50 | 2 | ¾ x 4¼ | 56.00 | 146.00 |
| 160 x 168.3 | | | 12.8 | 5.8 | 516.00 | 1032.00 | 130.50 | 2 | ¾ x 5 | 69.50 | 173.50 |
| 180 x 165.1 | | | 15.4 | 7.0 | 610.00 | 1220.00 | 148.00 | 2 | ¾ x 5 | 69.50 | 186.50 |
| 168.3 | | | 15.0 | 6.8 | 610.00 | 1220.00 | 148.00 | 2 | ¾ x 5 | 69.50 | 186.50 |
| 200 x 219.1 | | | 21.7 | 9.8 | 672.50 | 1345.00 | 166.00 | 2 | ¾ x 6¼ | 74.50 | 203.50 |
| 225 x 219.1 | | | 22.0 | 10.0 | 706.00 | 1412.00 | 178.50 | 2 | ¾ x 6¼ | 74.50 | 237.50 |
| 250 x 273.0 | | | 53.0 | 24.0 | 911.00 | 1822.00 | 225.00 | 4 | ⅞ x 6½ | 101.50 | 282.50 |
| 280 x 273.0 | | | 54.0 | 24.5 | 960.00 | 1920.00 | 237.50 | 4 | ⅞ x 6½ | 101.50 | 311.00 |
| 315 x 323.9 | | | 61.0 | 27.7 | 1009.00 | 2018.00 | 250.00 | 4 | ⅞ x 6½ | 101.50 | 339.00 |
| 355 x 355.6 | | | W907 | 81.0 | 36.7 | 1828.50 | 3657.00 | 424.50 | 4 | 1½ x 7 | 125.00 |

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

§ Price includes one bolt, nut, and washer for coupling sizes 2" - 8" | 63mm - 225mm and one bolt, nut, and two washers for coupling sizes 10" - 14" | 250mm - 355mm.

† One required for coupling sizes through 2" - 8" | 63mm - 225mm. Set of two required for coupling sizes 10" - 14" | 250mm - 355mm.

NOTE: Available with stainless steel bolts and nuts. Contact Victaulic for pricing.

* "Painted" option includes enamel coating with fluoropolymer-coated hardware. "Coated" option includes liquid bonded epoxy coating with stainless steel hardware.

NOTE: Fusion bonded epoxy and galvanized finishes available. Contact Victaulic for pricing.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com