

Price List Addendum

EFFECTIVE June 11, 2019

Models V4601 and V4603

**LP-46 STANDARD RESPONSE
LOW PRESSURE STORAGE**

**Upright and Pendent
1" NPT (25 mm) Thread / IGS™ Groove
K25.2 (36.8 SI)**

Refer to publication 40.95 for Model V4601.
Refer to publication 40.98 for Model V4603.



Upright
V4603 †



Pendent
V4601



Upright V4603 IGS
Grooved without
Style V9 Coupling



Temp. Rating		Threaded Connection				IGS Grooved with Style V9 Coupling				IGS Grooved without Style V9 Coupling			
		Victaulic Part Number		Price Each		Victaulic Part Number		Price Each		Victaulic Part Number		Price Each	
°F	°C	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent
Plain Brass Finish													
162	72	S4637NS910	S4638NS910	\$95.50	\$84.00	S46L7NS910	S46L8NS910	\$99.00	\$88.00	S46H7NS910	S46H8NS910	\$88.00	\$77.50
212	100	S4637GS910	S4638GS910	95.50	84.00	S46L7GS910	S46L8GS910	99.00	88.00	S46H7GS910	S46H8GS910	88.00	77.50
286	141	S4637JS910	S4638JS910	95.50	84.00	S46L7JS910	S46L8JS910	99.00	88.00	S46H7JS910	S46H8JS910	88.00	77.50

† LP-46 Model V4603 Upright is FM approved only.

Recommended Wrench: V46 Open End. See Accessories for part number and price.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Model V4902

EARLY SUPPRESSION FAST RESPONSE

**Pendent
1" IGS™ Groove (25 mm)
1" (25 mm) Orifice
K22.4 (32.0 SI)**

Refer to publication 40.92.



Pendent
V4902



Pendent V4902
with Style V9 Sprinkler
Coupling



Temp. Rating		IGS™ Grooved with Style V9 Coupling		IGS™ Grooved without Style V9 Coupling *	
		Victaulic Part Number	Price Each	Victaulic Part Number	Price Each
°F	°C	Pendent			
Plain Brass Finish					
164	74	S49LSDQM10	\$52.50	S49HSDQM10	\$42.00
212	100	S49LSGQM10	52.50	S49HSGQM10	42.00

* Available as spare parts in service or as sprinkler head replacement only.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

IGS™ Grooved Sprinklers

Model V4802

EARLY SUPPRESSION FAST RESPONSE

Pendent
1" IGS™ (25 mm) Grooved
K25.2 (36.8 SI)

Refer to publication 40.91.



Pendent
V4802

Pendent
V4802

Temp. Rating		IGS™ Grooved Sprinkler with Style V9 Coupling		IGS™ Grooved Sprinkler without Style V9 Coupling *	
		Victaulic Part Number	Price Each	Victaulic Part Number	Price Each
°F	°C	Pendent			
Plain Brass Finish					
155	68	S48LSCQ910	\$54.50	S48HSCQ910	\$44.00
200	93	S48LSFQ910	54.50	S48HSFQ910	44.00

Recommended Tool: Provided with the product, 3/16-inch hex installation bit.

* Available as spare parts in service work or as sprinkler head replacement only.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Model V4702

EARLY SUPPRESSION FAST RESPONSE

Pendent
3/4" NPT (20 mm) Thread / IGS™ Groove
3/4" (20 mm) Orifice
K16.8 (24.25 SI)

Refer to publication 40.89.



Pendent
V4702



Pendent V4702
with Style V9 Sprinkler
Coupling

Temp. Rating		Threaded Connection		IGS™ Grooved with Style V9 Coupling		IGS™ Grooved without Style V9 Coupling	
		Victaulic Part Number	Price Each	Victaulic Part Number	Price Each	Victaulic Part Number	Price Each
°F	°C	Pendent					
Plain Brass Finish							
155	68	S472SCQ810	\$39.50	S47KSCQ810	\$47.00	S47GSCQ810	\$36.50
200	93	S472SFQ810	39.50	S47KSFQ810	47.00	S47GSFQ810	39.50

Recommended Wrenches: V44; V47 Open End. See Accessories for part number and price.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

IGST™ Grooved Sprinklers

Models V3403 and V3407

**STANDARD RESPONSE
STORAGE –
EXTRA LARGE ORIFICE (ELO)**

**Upright and Pendent
¾" NPT (20 mm) Thread
⅝" (16 mm) Orifice
K11.2 (16.1 SI)**
Refer to publication 40.20.



Upright
V3403



Pendent
V3407



Upright
V3403
with Style
V9 Sprinkler
Coupling



Pendent
V3407
with Style
V9 Sprinkler
Coupling

Temp. Rating		Threaded Connection				IGS Grooved with Style V9 Coupling				IGS Grooved without Style V9 Coupling *			
°F	°C	Victaulic Part Number		Price Each		Victaulic Part Number		Price Each		Victaulic Part Number		Price Each	
		Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent
PLAIN BRASS FINISH													
135	57	S342AAS610	S342BAS610	\$69.00	\$69.00	-	-	-	-	-	-	-	-
155	68	S342ACS610	S342BCS610	69.00	69.00	S34KACS610	S34KBCS610	\$74.50	\$74.50	S34GACS610	S34GBCS610	\$63.50	\$63.50
175	79	S342AES610	S342BES610	69.00	69.00	-	-	-	-	-	-	-	-
200	93	S342AFS610	S342BFS610	69.00	69.00	S34KAFS610	S34KBFS610	80.50	74.50	S34GAFS610	S34GBFS610	63.50	63.50
286	141	S342AJS610	S342BJS610	69.00	69.00	S34KAJS610	S34KBJS610	74.50	74.50	S34GAJS610	S34GBJS610	63.50	63.50
Open		S342AMS610	S342BMS610	+	+								
CHROME													
135	57	S342AAS620	S342BAS620	\$79.50	\$79.50								
155	68	S342ACS620	S342BCS620	79.50	79.50								
175	79	S342AES620	S342BES620	79.50	79.50								
200	93	S342AFS620	S342BFS620	79.50	79.50								
286	141	S342AJS620	S342BJS620	79.50	79.50								
Open		S342AMS620	S342BMS620	+	+								
CUSTOM FINISH													
Victaulic proprietary coatings or customer to provide finish specifications. Allow 4-6 weeks for samples for customer finish specifications. See List Adders for Sprinklers at the beginning of this section													
135	57	S342AAS6_0	S342BAS6_0	+	+								
155	68	S342ACS6_0	S342BCS6_0	+	+								
175	79	S342AES6_0	S342BES6_0	+	+								
200	93	S342AFS6_0	S342BFS6_0	+	+								
286	141	S342AJS6_0	S342BJS6_0	+	+								
Open		S342AMS6_0	S342BMS6_0	+	+								

+ Quoted on application. Contact Victaulic for pricing and availability.

Recommended Wrenches: V34 Open End; V34 Recessed. See Accessories for part number and pricing.

NOTE: When applicable, VC-250 should be used in conjunction with stainless steel escutcheons.

* Available as spare parts only.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

IGS™ Grooved Sprinklers

Models V3404 and V3408

**QUICK RESPONSE
STORAGE –
EXTRA LARGE ORIFICE (ELO)**

**Upright and Pendent
¾" NPT (20 mm) Thread
⅝" (16 mm) Orifice
K11.2 (16.1 SI)**
Refer to publication 40.20.



Upright
V3404



Pendent
V3408



Upright
V3404
with Style
V9 Sprinkler
Coupling



Pendent
V3408
with Style
V9 Sprinkler
Coupling

Temp. Rating		Threaded Connection				IGS Grooved with Style V9 Coupling				IGS Grooved without Style V9 Coupling			
		Victaulic Part Number		Price Each		Victaulic Part Number		Price Each		Victaulic Part Number		Price Each	
°F	°C	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent	Upright	Pendent
PLAIN BRASS FINISH													
135	57	S342AAQ610	S342BAQ610	\$91.00	\$91.00	–	–	–	–	–	–	–	–
155	68	S342ACQ610	S342BCQ610	91.00	91.00	S34KACQ610	S34KBCQ610	\$94.50	\$94.50	S34GACQ610	S34GBCQ610	\$84.00	\$84.00
175	79	S342AEQ610	S342BEQ610	91.00	91.00	–	–	–	–	–	–	–	–
200	93	S342AFQ610	S342BFQ610	91.00	91.00	S34KAFQ610	S34KBFQ610	94.50	94.50	S34GAFQ610	S34GBFQ610	84.00	84.00
286	141	S342AJQ610	S342BJQ610	91.00	91.00	S34KAJQ610	S34KBQ610	94.50	94.50	S34GAJQ610	S34GBQ610	84.00	84.00
CHROME													
135	57	S342AAQ620	S342BAQ620	\$100.00	\$100.00	–	–	–	–	–	–	–	–
155	68	S342ACQ620	S342BCQ620	100.00	100.00	–	–	–	–	–	–	–	–
175	79	S342AEQ620	S342BEQ620	100.00	100.00	–	–	–	–	–	–	–	–
200	93	S342AFQ620	S342BFQ620	100.00	100.00	–	–	–	–	–	–	–	–
286	141	S342AJQ620	S342BJQ620	100.00	100.00	–	–	–	–	–	–	–	–
CUSTOM FINISH													
Victaulic proprietary coatings or customer to provide finish specifications. Allow 4-6 weeks for samples for customer finish specifications. See List Adders for Sprinklers at the beginning of this section													
135	57	S342AAQ6_0	S342BAQ6_0	+	+	–	–	–	–	–	–	–	–
155	68	S342ACQ6_0	S342BCQ6_0	+	+	–	–	–	–	–	–	–	–
175	79	S342AEQ6_0	S342BEQ6_0	+	+	–	–	–	–	–	–	–	–
200	93	S342AFQ6_0	S342BFQ6_0	+	+	–	–	–	–	–	–	–	–
286	141	S342AJQ6_0	S342BJQ6_0	+	+	–	–	–	–	–	–	–	–

Recommended Wrenches: V34 Open End; V34 Recessed. See Accessories for part number and pricing.

NOTE: When applicable, VC-250 should be used in conjunction with stainless steel escutcheons.

+ Quoted on application. Contact Victaulic for pricing and availability.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com