

# Price List Addendum

EFFECTIVE March 15, 2022



PL2022-GEN-ADD4

## QuickVic™ System

### QuickVic™ Rigid Coupling

#### STYLE 107V

Refer to publication 06.33



#### STYLE 107V – GRADE “EHP” GASKET

PIPE		Approx. Wgt. Ea. lb	COUPLING COMPLETE † With Grade “EHP” Gasket Price Each	SPARE PARTS			
inches				Grade “EHP” Gasket	Plated Bolt & Nut		
Nom. Size	Outside Dia.		Painted			No.	Size inches
2	2.375	2.9	\$125.00	\$98.00 <sup>NR</sup>	2	1/2 x 2 3/4	\$39.50
2 1/2	2.875	3.3	141.50	106.00 <sup>NR</sup>	2	1/2 x 2 3/4	39.50
3	3.500	3.7	163.50	120.00 <sup>NR</sup>	2	1/2 x 3	39.50
4	4.500	5.0	226.50	160.00 <sup>NR</sup>	2	1/2 x 3	39.50
6	6.625	8.1	381.50	266.50 <sup>NR</sup>	2	5/8 x 3 5/8	75.00
8	8.625	16.1	602.50	320.50 <sup>NR</sup>	2	3/4 x 5	137.50
10	10.750	24.7	1166.00	370.00 <sup>NR</sup>	2	7/8 x 6 1/2	245.00
12	12.750	29.1	1302.00	411.00 <sup>NR</sup>	2	7/8 x 6 1/2	245.00

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

<sup>NR</sup> Non-returnable

Orders for the Style 107N QuickVic™ Rigid Coupling may be automatically substituted for the Style 107V QuickVic™ Rigid Coupling at Victaulic's discretion.

### QuickVic™ Elbows

Refer to publication 07.14



No. V10



No. V11

#### ELBOWS – 90° ELBOW OR 45° ELBOW

Nom. Size inches	Approx. Wgt. Ea. lb	90° Elbow No. V10		Approx. Wgt. Ea. lb	45° Elbow No. V11	
		Price Each			Price Each	
		Painted	Galv.		Painted	Galv.
2	1.5	\$45.00	\$61.00	1.2	\$45.00	\$61.00
2 1/2	2.2	52.50	71.00	1.7	52.50	71.00
3	2.9	82.50	111.50	2.3	82.50	111.50
4	4.4	101.00	136.50	3.7	101.00	136.50
6	10.8	157.50	213.00	7.4	157.50	213.00
8	25.4	237.50	321.00	18.9	160.00	216.00
10	41.0	256.50	346.50	25.0	166.50	225.00
12	66.3	368.00	497.00	35.9	260.50	352.00



QuickVic™ Tee

Refer to publication 07.14



No. V20

STANDARD TEE

Nom. Size	Approx. Wgt. Ea.	Tee No. V20	
		Price Each	
inches	lb	Painted	Galv.
2	2.1	\$70.50	\$95.50
2½	2.2	78.00	105.50
3	4.8	99.00	134.00
4	6.0	169.50	229.00
6	20.0	254.00	343.00
8	36.9	287.50	388.50
10	63.6	306.50	414.00
12	90.3	520.50	703.00

QuickVic™ 90° Elbow Flanged Adapter Modules

NO. V15 – ANSI CLASS 150

Refer to publication 07.14



90° ELBOW FLANGED ADAPTER MODULES – ANSI CLASS 150

Nom. Size	ANSI Class 150	No. V15F (Flat Face)		No. V15R (Raised Face)	
	Approx. Wgt. Ea.	Module Complete with Grade "EHP" Gasket		Module Complete with Grade "EHP" Gasket	
inches	lb	Price Each		Price Each	
		Painted	Galv.	Painted	Galv.
2	10.2	\$266.50	\$328.50	\$266.50	\$328.50
2½	14.9	327.00	409.00	327.00	409.00
3	18.1	379.00	477.00	379.00	477.00
4	27.7	495.50	625.50	495.50	625.50
6	45.4	657.00	779.50	657.00	779.50
8	82.4	801.50	1043.50	801.50	1043.50
10	129.8	1147.00	1478.00	1147.00	1478.00
12	183.2	1532.00	1992.50	1532.00	1992.50

QuickVic™ 90° Elbow Flanged Adapter Modules

NO. V16 – ANSI CLASS 300

Refer to publication 07.14



90° ELBOW FLANGED ADAPTER MODULES – ANSI CLASS 300

Nom. Size	ANSI Class 300	No. V16F (Flat Face)		No. V16R (Raised Face)	
	Approx. Wgt. Ea.	Module Complete with Grade "EHP" Gasket		Module Complete with Grade "EHP" Gasket	
inches	lb	Price Each		Price Each	
		Painted	Galv.	Painted	Galv.
2	12.4	\$321.50	\$385.00	\$321.50	\$385.00
2½	16.9	372.00	452.00	372.00	452.00
3	22.9	519.00	628.00	519.00	628.00
4	36.6	680.50	838.50	680.50	838.50
6	65.4	924.50	1152.00	924.50	1152.00
8	111.4	1116.00	1428.50	1116.00	1428.50
10	166.6	1654.50	2084.00	1654.50	2084.00
12	241.4	1860.50	2422.00	1860.50	2422.00

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com