

# Price List Addendum

EFFECTIVE January 31, 2022

## Fire Protection Valves and Devices

### Universal Manifold Check Assembly

#### SERIES UMC

Includes Series UTD Test and Drain, and Series ARV Adjustable Relief Valve.

Refer to publication 30.72.



#### SERIES UMC – UNIVERSAL MANIFOLD CHECK ASSEMBLY

UMC Body Size	Description	Part Code	Price Each
Nominal inches			
1¼	GxG Right Handed with Control Valve and Hose	S012UMCRV0	\$1591.50
	GxG Right Handed with Hose	S012UMCR00	1389.00
	GxG Left Handed with Control Valve and Hose	S012UMCLV0	1591.50
	GxG Left Handed with Hose	S012UMCL00	1389.00
1½	GxG Right Handed with Control Valve and Hose	S014UMCRV0	1662.50
	GxG Right Handed with Hose	S014UMCR00	1427.50
	GxG Left Handed with Control Valve and Hose	S014UMCLV0	1662.50
	GxG Left Handed with Hose	S014UMCL00	1427.50
2	GxG Right Handed with Control Valve and Hose	S020UMCRV0	1844.50
	GxG Right Handed with Hose	S020UMCR00	1572.50
	GxG Left Handed with Control Valve and Hose	S020UMCLV0	1844.50
	GxG Left Handed with Hose	S020UMCL00	1572.50
2½	GxG Right Handed with Control Valve and Hose	S024UMCRV0	1878.00
	GxG Right Handed with Hose	S024UMCR00	1606.50
	GxG Left Handed with Control Valve and Hose	S024UMCLV0	1878.00
	GxG Left Handed with Hose	S024UMCL00	1606.50
3	GxG Right Handed with Control Valve and Hose	S030UMCRV0	2169.50
	GxG Right Handed with Hose	S030UMCR00	1934.50
	GxG Left Handed with Control Valve and Hose	S030UMCLV0	2169.50
	GxG Left Handed with Hose	S030UMCL00	1934.50
4	GxG Right Handed with Control Valve and Hose	S040UMCRV0	2318.00
	GxG Right Handed with Hose	S040UMCR00	2085.50
	GxG Left Handed with Control Valve and Hose	S040UMCLV0	2318.00
	GxG Left Handed with Hose	S040UMCL00	2085.50
6	GxG Right Handed with Control Valve and Hose	S060UMCRV0	2876.50
	GxG Right Handed with Hose	S060UMCR00	2511.00
	GxG Left Handed with Control Valve and Hose	S060UMCLV0	2876.50
	GxG Left Handed with Hose	S060UMCL00	2511.00
8	GxG Right Handed with Control Valve and Hose	S080UMCRV0	4348.50
	GxG Right Handed with Hose	S080UMCR00	3520.50

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

#### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com