

Victaulic Component

1/2 HP Compressor Series 7C7
1/3 HP Compressor Series 7C7
1/6 HP Compressor Series 7C7
11-1/4 Deg. Elbow No.13-C (AWWA)
22-1/2 Deg. Elbow No.12-C (AWWA)
3/4 HP Compressor Series 7C7
45 Deg. Elbow No. 11-P
45 deg. Elbow No.003
45 deg. Elbow No.11
45 Deg. Elbow No.11-C (AWWA)
45 Deg. Lateral No. 30-C (AWWA)
45 Deg. Lateral No. 30-P (Plain End)
45 Deg. Long Tangent Elbow No. 11-PS
90 Deg. Elbow No. 10-P
90 Deg. Elbow No. 610 (CTS)
90 deg. Elbow No.001
90 deg. Elbow No.10
90 Deg. Elbow No.10-C (AWWA)
90 Deg. Elbow No.610 (CTS)
90 Deg. Long Tangent Elbow No. 10-PS
90 Deg. LR Elbow No.100-C (AWWA)
90 Deg. Red. Elbow No.10-CR (AWWA)
90° No.10-DR
Air Maintenance Trim Assembly Series 757
Air Maintenance Trim Assembly Series 757-P
Boltless Coupling Style 791
Brass Body Ball Valve series 722
Bull plug No. 61-P
Cap No. 660(CTS)
Cap No.006
Cap No.60
Cap No.60-C (AWWA)
Copper Grooved 45° Elbow
Coupling Flex style 75
Coupling Flex style 77
Coupling Rigid style 07
Coupling Rigid style HP-70
Coupling style 31
Coupling Style 606 (CTS)
Coupling Style 607(CTS)
Coupling Style 995N (HDPE)
Cross No. 35-P

Victaulic Component

Cross No.35-C (AWWA)
Double Pneumatic Actuator Series 798
Electric / Pneumatic Double Interlock Actuator Series 767
FireLock 300 PSI Solenoid Series 753-E
FireLock Alarm Check Valve Series 751 (G x G)
FireLock Alarm Check Valve Series 751 (G x G) (Europe Only)
FireLock Alarm Check Valve Series 759 (Canada Only)
FireLock Alarm Check Valve Series 759 (Standard Trim)
Firelock Ball Valve series 728 THD
Firelock Ball Valves series 728 GRV
Firelock Butterfly Valve series 705 W
Firelock Butterfly Valve series 707-C W
Firelock Check Valve series 717
Firelock Check Valve series 717-H
FireLock Check Valve Series 717HR
FireLock Check Valve Series 717R
FireLock Commercial Zone Control Riser Module Series 747M
FireLock Dry Accelerator Series 746
FireLock Dry Actuator / Anti-Flood Device Series 753-A
FireLock Fire Pump Test Meter Style 735L
FireLock Fire Pump Test Meter Style 735S
FireLock Fire-Pac Series 745
Firelock High pressure Butterfly Valve series 765
Firelock High pressure Butterfly Valves series 766
FireLock Low Profile Sprinkler Tee Style 912
FireLock NRS Upright Post Indicator Series 774
FireLock NRS Wall Post Indicator Series 773
FireLock NXT Deluge Valve Series 769
FireLock NXT Dry Valve Series 768
FireLock NXT Preaction Valve Series 769 (LPCB Approved)
FireLock NXT Preaction Valve With Double Interlock Pneumatic / Electric Actuators Series 769
FireLock NXT Preaction Valve With Low Pressure Actuators Series 769
FireLock NXT Wet / Dry Valve Series 764
FireLock Residential Zone Control Riser Module Series 247
FireLock Retard Chamber Series 752
Firelock Tee No.002
FireLock V10 Window Sprinkler, V1001, K1.4
FireLock V10 Window Sprinkler, V1003, K1.9
FireLock V10 Window Sprinkler, V1005, K2.8
FireLock V10 Window Sprinkler, V1007, K4.2
FireLock V10 Window Sprinkler, V1009, K5.6
FireLock V10 Window Sprinkler, V1011, K8.0
FireLock V10 Window Sprinkler, V1013, K11.2

Victaulic Component

FireLock Water Motor Alarm Series 760
FireLock(TM) Installation-Ready(TM) 45° Elbow
FireLock(TM) Installation-Ready(TM) 90° Elbow
Flange adapter style 341
Flange adapter style 641 (CTS)
Flange adapter style 741
Flange adapter style 743
Flange adapter style 744
Flange adapter Style 994(HDPE)
Gate Valve series 771F OS&Y
Gate Valve series 771H OS&Y
Gate Valve series 772F NRS
Gate Valve series 772H NRS
Low Pressure Actuator Series 776
Mechanical-T Outlet Grooved style 920
Mechanical-T Outlet Grooved style 920N
Mechanical-T Outlet style 922 Firelock (THD)
Mechanical-T Outlet Threaded style 920
Mechanical-T Outlet threaded style 920N
Open Spray Nozzle
Open Spray Nozzle, V1201, K1.2
Open Spray Nozzle, V1202, K1.2
Open Spray Nozzle, V1203, K1.2
Open Spray Nozzle, V1204, K1.2
Open Spray Nozzle, V1205, K1.2
Open Spray Nozzle, V1206, K1.2
Open Spray Nozzle, V1207, K1.2
Open Spray Nozzle, V1208, K1.2
Open Spray Nozzle, V1211, K1.8
Open Spray Nozzle, V1212, K1.8
Open Spray Nozzle, V1213, K1.8
Open Spray Nozzle, V1214, K1.8
Open Spray Nozzle, V1215, K1.8
Open Spray Nozzle, V1216, K1.8
Open Spray Nozzle, V1217, K1.8
Open Spray Nozzle, V1218, K1.8
Open Spray Nozzle, V1221, K2.3
Open Spray Nozzle, V1222, K2.3
Open Spray Nozzle, V1223, K2.3
Open Spray Nozzle, V1224, K2.3
Open Spray Nozzle, V1225, K2.3
Open Spray Nozzle, V1226, K2.3
Open Spray Nozzle, V1227, K2.3

Victaulic Component

Open Spray Nozzle, V1228, K2.3
Open Spray Nozzle, V1231, K3.2
Open Spray Nozzle, V1232, K3.2
Open Spray Nozzle, V1233, K3.2
Open Spray Nozzle, V1234, K3.2
Open Spray Nozzle, V1235, K3.2
Open Spray Nozzle, V1236, K3.2
Open Spray Nozzle, V1237, K3.2
Open Spray Nozzle, V1238, K3.2
Open Spray Nozzle, V1241, K4.1
Open Spray Nozzle, V1242, K4.1
Open Spray Nozzle, V1243, K4.1
Open Spray Nozzle, V1244, K4.1
Open Spray Nozzle, V1245, K4.1
Open Spray Nozzle, V1246, K4.1
Open Spray Nozzle, V1247, K4.1
Open Spray Nozzle, V1248, K4.1
Open Spray Nozzle, V1251, K4.9
Open Spray Nozzle, V1252, K4.9
Open Spray Nozzle, V1253, K4.9
Open Spray Nozzle, V1254, K4.9
Open Spray Nozzle, V1255, K4.9
Open Spray Nozzle, V1256, K4.9
Open Spray Nozzle, V1257, K4.9
Open Spray Nozzle, V1258, K4.9
Open Spray Nozzle, V1261, K5.6
Open Spray Nozzle, V1262, K5.6
Open Spray Nozzle, V1263, K5.6
Open Spray Nozzle, V1264, K5.6
Open Spray Nozzle, V1265, K5.6
Open Spray Nozzle, V1266, K5.6
Open Spray Nozzle, V1267, K5.6
Open Spray Nozzle, V1268, K5.6
Open Spray Nozzle, V1271, K7.2
Open Spray Nozzle, V1272, K7.2
Open Spray Nozzle, V1273, K7.2
Open Spray Nozzle, V1274, K7.2
Open Spray Nozzle, V1275, K7.2
Open Spray Nozzle, V1276, K7.2
Open Spray Nozzle, V1277, K7.2
Open Spray Nozzle, V1278, K7.2
Outlet Coupling Style 72 FPT
Pendent, 80.73, (STD)

Victaulic Component

Reducer Concentric No.50-C (AWWA)
Reducing Coupling style 750
Reducing Tee No. 25
Reducing Tee No.25-C (AWWA)
Roust-A-Bout Coupling Style 99
series 7B2 Butterfly valve gear operator
style 005H Firelock Rigid Coupling
style 009H Firelock EZ Rigid Coupling
style 009N Firelock Rigid Coupling
Supplemental Alarm Kit Series 75B
Supplemental Alarm Kit Series 75D
Tee No.20
Tee No.20-C (AWWA)
TestMaster II Alarm Test Module Style 720
Transition Coupling style 307
Transition Coupling style 997 (HDPE)
True Wye No. 33-P (Plain End)
Upright, 80.73, (STD)
V2502, 4.2, Upright, (QR)
V2601, 2.8, Pendent, (OPEN)
V2603, 5.6, Pendent, (OPEN)
V2701, 2.8, Upright, (STD)
V2702, 2.8, Upright, (QR)
V2703, 5.6, Upright, (STD)
V2703-E, 5.6, Upright, (STD)
V2704, 5.6, Upright, (QR)
V2704-E, 5.6, Upright, (QR)
V2705, 2.8, Pendent, (STD)
V2705-R, 2.8, Pendent, (STD)
V2706, 2.8, Pendent, (QR)
V2706-R, 2.8, Pendent, (QR)
V2707, 5.6, Pendent, (STD)
V2707-R, 5.6, Pendent, (STD)
V2708, 5.6, Pendent, (QR)
V2708-R, 5.6, Pendent, (QR)
V2709, 5.6, Sidewall, (STD)
V2709-R, 5.6, Sidewall, (STD)
V2710, 5.6, Sidewall, (QR)
V2710-R, 5.6, Sidewall, (QR)
V2710-RA, 5.6, Sidewall, (QR)
V2721, 5.6, Upright, (STD)
V2721-G, 5.6, Upright, (STD)
V2722, 5.6, Upright, (QR)

Victaulic Component

V2722-G, 5.6, Upright, (QR)
V2723, 5.6, Pendent, (STD)
V2724, 5.6, Pendent, (QR)
V2725, 5.6, Pendent, (STD)
V2725, 5.6, Upright, (STD)
V2725-E, 5.6, Pendent, (STD)
V2725-E, 5.6, Upright, (STD)
V2725-E, 80.73, Pendent, (STD)
V2725-E, 80.73, Upright, (STD)
V2726, 5.6, Pendent, (QR)
V2726, 5.6, Upright, (QR)
V2726, 80.73, Pendent, (QR)
V2726, 80.73, Upright, (QR)
V2726-E, 5.6, Pendent, (QR)
V2726-E, 5.6, Upright, (QR)
V2726-E, 80.73, Pendent, (QR)
V2727-E, 80.73, Pendent, (STD)
V2728-E, 80.73, Pendent, (QR)
V2730, 4.9, Pendent, (QR)
V2730-R, 4.9, Pendent, (QR)
V2732, 4.9, Pendent, (QR)
V2732-R, 4.9, Pendent, (QR)
V2738, 4.2, Sidewall, (QR)
V2738-R, 4.2, Sidewall, (QR)
V2740, 4.9, Pendent, (QR)
V2740-R, 4.9, Pendent, (QR)
V2740-RA, 4.9, Pendent, (QR)
V2742, 4.9, Pendent, (QR)
V2742, 4.9, Pendent, (QR)
V2744-R, 5.6, Sidewall, (QR)
V2744-RA, 5.6, Sidewall, (QR)
V2902-E, 4.1, Pendent, (QR)
V3102, 8, Pendent, (QR)
V3104, 11.2, Pendent, (QR)
V3301, 5.6, Pendent, (STD)
V3302, 5.6, Pendent, (QR)
V3303, 8, Pendent, (STD)
V3304, 8, Pendent, (QR)
V3401, 8, Upright, (STD)
V3401-E, 8, Upright, (STD)
V3402, 8, Upright, (QR)
V3402-E, 8, Upright, (QR)
V3403, 11.2, Upright, (STD)

Victaulic Component

V3404, 11.2, Upright, (QR)
V3405, 8, Pendent, (STD)
V3405-R, 8, Pendent, (STD)
V3406, 8, Pendent, (QR)
V3406-R, 8, Pendent, (QR)
V3406-RA, 8, Pendent, (QR)
V3407, 11.2, Pendent, (STD)
V3408, 11.2, Pendent, (QR)
V3409, 8, Sidewall, (STD)
V3409-R, 8, Sidewall, (STD)
V3410, 8, Sidewall, (QR)
V3410-R, 8, Sidewall, (QR)
V3411, 11.2, Pendent, (STD)
V3411-R, 11.2, Pendent, (STD)
V3411-RA, 11.2, Pendent, (STD)
V3412, 11.2, Pendent, (QR)
V3412-R, 11.2, Pendent, (QR)
V3412-RA, 11.2, Pendent, (QR)
V3413, 14, Pendent, (STD)
V3413-R, 14, Pendent, (STD)
V3413-RA, 14, Pendent, (STD)
V3414, 14, Pendent, (QR)
V3414-R, 14, Pendent, (QR)
V3414-RA, 14, Pendent, (QR)
V3415, 8, Sidewall, (STD)
V3415-R, 8, Sidewall, (STD)
V3415-RA, 8, Sidewall, (STD)
V3416, 8, Sidewall, (QR)
V3416-R, 8, Sidewall, (QR)
V3416-RA, 8, Sidewall, (QR)
V3417, 8, Upright, (STD)
V3417-G, 8, Upright, (STD)
V3418, 8, Upright, (QR)
V3418-G, 8, Upright, (QR)
V3419, 8, Pendent, (STD)
V3420, 8, Pendent, (QR)
V3421, 14, Pendent, (STD)
V3421-RA, 14, Pendent, (STD)
V3423, 11.5, Pendent, (STD)
V3424, 11.5, Pendent, (QR)
V3426, 6.9, Pendent, (QR)
V3426-R, 6.9, Pendent, (QR)
V3428, 8, Pendent, (QR)

Victaulic Component

V3601, 5.6, Upright, (STD)
V3602, 5.6, Upright, (QR)
V3603, 115.33, Upright, (STD)
V3603, 8.1, Upright, (STD)
V3604, 8.1, Upright, (QR)
V3605-E, 5.6, Pendent, (STD)
V3605-F, 5.6, Pendent, (STD)
V3605-I, 5.6, Pendent, (STD)
V3605-P, 5.6, Pendent, (STD)
V3605-R, 5.6, Pendent, (STD)
V3605-S, 5.6, Pendent, (STD)
V3606-E, 5.6, Pendent, (QR)
V3606-F, 5.6, Pendent, (QR)
V3606-I, 5.6, Pendent, (QR)
V3606-P, 5.6, Pendent, (QR)
V3606-R, 5.6, Pendent, (QR)
V3606-S, 5.6, Pendent, (QR)
V3607-E, 8, Pendent, (STD)
V3607-F, 8, Pendent, (STD)
V3607-I, 8, Pendent, (STD)
V3607-P, 8, Pendent, (STD)
V3607-R, 8, Pendent, (STD)
V3607-S, 8, Pendent, (STD)
V3608-E, 8, Pendent, (QR)
V3608-F, 8, Pendent, (QR)
V3608-I, 8, Pendent, (QR)
V3608-P, 8, Pendent, (QR)
V3608-R, 8, Pendent, (QR)
V3608-S, 8, Pendent, (QR)
V3609-E, 5.6, Sidewall, (STD)
V3609-F, 5.6, Sidewall, (STD)
V3609-R, 5.6, Sidewall, (STD)
V3609-S, 5.6, Sidewall, (STD)
V3610-E, 5.6, Sidewall, (QR)
V3610-F, 5.6, Sidewall, (QR)
V3610-P, 5.6, Sidewall, (QR)
V3610-R, 5.6, Sidewall, (QR)
V3610-S, 5.6, Sidewall, (QR)
V3611-E, 8, Sidewall, (STD)
V3611-F, 8, Sidewall, (STD)
V3611-P, 8, Sidewall, (STD)
V3611-R, 8, Sidewall, (STD)
V3611-S, 8, Sidewall, (STD)

Victaulic Component

V3612-E, 8, Sidewall, (QR)
V3612-F, 8, Sidewall, (QR)
V3612-P, 8, Sidewall, (QR)
V3612-R, 8, Sidewall, (QR)
V3612-S, 8, Sidewall, (QR)
V3617, 5.6, Pendent, (STD)
V3618, 5.6, Pendent, (QR)
V3801, 5.6, Pendent, (STD)
V3801, 5.6, Pendent, (STD)
V3801, 80.73, Pendent, (STD)
V3801-A, 5.6, Pendent, (STD)
V3802, 5.6, Pendent, (QR)
V3802, 5.6, Pendent, (QR)
V3802, 80.73, Pendent, (QR)
V3802-A, 5.6, Pendent, (QR)
V3806, 5.6, Pendent, (QR)
V3807, 5.6, Pendent, (STD)
V3808, 5.6, Pendent, (QR)
V3904, 8, Pendent, (QR)
V4601, 25.2, Pendent, (STD)
V4603, 25.2, Upright, (STD)
Vic-Flex AQB-Braided
Vic-Flex AQC-Braided
Vic-Flex AQD-Braided
Vic-Flex AQU
Vic-Strainer FireLock Wye Type Style 732H
Vortex 500 Fire Suppression System