

PRODUCT FEATURES



AQUAMINE... THE RIGHT PIPE FOR THE RIGHT JOB


Introducing the Aquamine® system. Aquamine is a complete line of high impact resistant, reusable PVC pipe, fittings, valves and specialty items. Because of its superior strength and flexibility as

well as other critically important features, Aquamine has become one of the leading products in its field, consistently providing the competitive edge in efficiency and productivity.

With expanded industrial applications in construction, agriculture/irrigation and mining, Aquamine is available through a network of helpful, knowledgeable distributors worldwide.

THE PRODUCT

- Synthetic rubber o-ring provides chemical resistance for a wide range of services
- High impact resistant PVC pipe and coupling provide strong piping components
- Spline assembly combines maximum strength by engaging into grooves in both the coupling and the pipe
- Thickened pipe end provides joint reinforcement and security



© Aquamine and Victaulic are Registered Trademarks of Victaulic Company of America and its affiliates
© Copyright 2000 Victaulic Company of America and its affiliates Printed in U.S.A.

FEATURES AND BENEFITS

Features	Benefits
Low Cost ... compared to aluminum or steel pipe.	Lower total installed cost compared to most other types of piping systems.
Easy to Install ... no special skills, tools or equipment.	Lower total installed cost compared to most other types of piping systems.
Lighter Weight ... less than steel. ... less than HDPE	Easier to handle and to move in tight spaces.
Reusable ... disconnects as easy as it connects.	Economical
Rust-free ... compared to steel pipe.	Low maintenance and the flow rate does not deteriorate over time.
SDR Sized Pipe ... provides consistent pressure class and rating for the piping system.	Reliable
Self-restraining joint	No exterior restraints or thrust blocks.

PIPING, SIMPLE TO INSTALL. VALUE, DIFFICULT TO MATCH.

The ideal piping system for applications where. . .

- The piping must be re-deployed
- Corrosion resistance is required
- The speed of installation is essential
- Pipe sections must be hand carried

Typical applications

- Temporary water bypass lines
- Mine water supply and discharge
- Acid wastes
- Heap leaching
- Dewatering systems
- Coal prep plants
- Brine solution transport
- Sludge and slurry lines
- Dredging
- Crop irrigation
- Horizontal directional drilling
- Timber wet deck systems
- Overland restrained joint piping
- Potable water systems
- Emergency piping
- Golf course irrigation
- River and creek crossings



Aquamine products are sold through a network of Aquamine distributors located throughout the United States.

For information on the distributor near you, please call:

1-800-637-0117

Internationally, Aquamine products are available through:

Victaulic World Headquarters

P.O. Box 31 • Easton, PA 18044-0031
4901 Kesslersville Road • Easton, PA USA 18040
Phone: 610/559-3300 • FAX: 610/250-8817

Victaulic Company of Canada

Canadian Headquarters
65 Worcester Road • Rexdale, Ontario • Canada M9W 5N7
Phone: 416/675-5575 • FAX: 416/675-5565

Victaulic International

P.O. Box 31 • Easton, PA, USA 18044-0031
4901 Kesslersville Road • Easton, PA, USA 18040
Phone: 610/559-3300 • FAX: 610/559-3608

Victaulic Europe

Prijkelstraat 36 • 9810 Nazareth Belgium
Phone: 011-32-93-811500 • FAX: 011-32-93-804438