



TOP VIEW




FRONT VIEW



FRONT VIEW
DOOR NOT SHOWN
(6" SHOWN OTHER SIZES SIMILAR)

FIRELOCK FIRE-PAC




RIGHT SIDE VIEW


NOMINAL SIZE INCHES mm	ACTUAL OUTSIDE DIAMETER INCHES mm	HEIGHT A	WIDTH B	DEPTH C	D	E	F	G*	H*	I*	J*	K	L	M	APPROXIMATE WEIGHT EACH lbs/kg
1½ 40	1.900 48.3	69.11 1755.4	23.62 599.9	19.89 505.2	12.00 304.8	9.63 244.6	9.69 246.1	10.05 255.3	9.92 252.0	14.42 366.3	10.43 264.9	2.52 64.0	7.06 179.3	3.00 76.2	350.0 158.8
2 50	2.375 60.3	69.11 1755.4	23.62 599.9	19.89 505.2	12.00 304.8	9.63 244.6	9.69 246.1	10.05 255.3	9.92 252.0	14.42 366.3	10.43 264.9	2.20 55.9	7.56 192.0	3.00 76.2	360.0 163.3
2½ 65	2.875 73.0	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	4.47 113.5	4.47 113.5	3.00 76.2	516.0 234.1
76.1mm	3.000 76.1	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	4.47 113.5	4.47 113.5	3.00 76.2	516.0 234.1
3 80	3.500 88.9	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	5.57 141.5	5.57 141.5	3.00 76.2	522.0 236.8
4 100	4.500 114.3	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	5.73 145.5	5.40 137.2	3.00 76.2	720.0 326.6
165.1mm	6.500 165.1	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	3.85 97.8	3.85 97.8	3.00 76.2	840.0 381.0
6 150	6.625 168.3	69.11 1755.4	31.50 800.1	23.81 604.8	12.00 304.8	15.75 400.1	8.84 224.5	12.15 308.6	8.84 224.5	16.67 423.4	11.62 295.1	3.85 97.8	3.85 97.8	3.00 76.2	840.0 381.0

* DIMENSIONS G, H, I, AND J APPLY TO BOTH SIDE VIEWS OF THE CABINET

PRODUCT LEGEND	
1	ELECTRICAL ENCLOSURE
2	DIAPHRAGM PRESSURE GAUGE
3	SYSTEM AIR PRESSURE GAUGE
4	WATER SUPPLY PRESSURE GAUGE
5	UPPER CHAMBER PRESSURE GAUGE FOR THE SERIES 767 ELECTRIC/PNEUMATIC ACTUATOR
6	REMOVABLE SIDE PANNELS
7	FIRE ALARM CONTROL PANEL*
8	MANUAL PULL STATION
9	RISER OPENING OUT TO SYSTEM
10	LIFTING EYHOOKS
11	ELECTRICAL KNOCKOUT NON-POWER LIMITED
12	ELECTRICAL KNOCKOUT POWER LIMITED
13	CABNET KNOCKOUT FOR DRAIN CONNECTION (LOCATED ON BOTH SIDES)
14	CABNET KNOCKOUT FOR WATER SUPPLY (LOCATED ON BOTH SIDES)
15	RISER FEED PIPE OUT TO SYSTEM
16	AIR COMPRESSOR*
17	AIR MANIFOLD
18	ALARM PRESSURE SWITCH
19	DIAPHRAGM CHARGE-LINE BALL VALVE
20	DRIP CUP WITH CAP
21	DRAIN CONNECTION FOR MULTI-UNIT INSTALLATIONS
22	WATER SUPPLY CONNECTION FOR MULTI-UNIT INSTALLATIONS
23	TO DRAIN CONNECTION
24	FROM WATER SUPPLY
25	MANUAL PULL STATION
26	WATER SUPPLY MAIN CONTROL VALVE
27	WATER SUPPLY MAIN DRAIN VALVE
28	SYSTEM MAIN DRAIN VALVE
29	AIR SUPERVISORY PRESSURE SWITCH
30	AIR TANK BLEED VALVE
31	ADDITIONAL WATER SUPPLY MAIN CONTROL VALVE*
32	AIR TANK*
SEE VICTAULIC SUBMITTAL NUMBER 30.23 AND I-745	



NOTES:
1. REFER TO VICTAULIC SUBMITTAL 10.92 FOR ADDITIONAL DETAILS.
2. * OPTIONAL EQUIPMENT.



Victaulic CONSTRUCTION PIPING SERVICES DIVISION

PROJECT: FIRELOCK FIRE-PAC PROJ.# _____
 CUSTOMER: _____ P.O.# _____
 SYSTEM: SERIES 745 FIREPAC
 REF. DWG.: VICTAULIC SUBMITTAL 30.23 #039

DRN.BY: RGS	DATE: 05/07/09	DRAWING NUMBER	REV.
CHK.BY: .	DATE: .	745-FIREPAC	H