

Victaulic® Long Radius Steel Elbows 3D, 5D and 6D



Product Description

Victaulic® long radius elbows are formed from standard wall steel pipe to ASTM A-53 Grade B. Fittings are painted orange enamel with galvanized optionally available.

Elbows are supplied with standard cut grooves unless otherwise requested. They are also available with plain ends by request.

Job/Owner

| | |
|------------|--|
| System No. | |
| Location | |

Contractor


| | |
|--------------|--|
| Submitted By | |
| Date | |

Engineer

| | |
|--------------|--|
| Spec Section | |
| Paragraph | |
| Approved | |
| Date | |

Dimensions

Long Radius Steel Elbows - 3D



| Fitting Size | | No. 100- 3D 90° | | No. 14- 3D 60° | | No. 110- 3D 45° | | No. 15- 3D 30° | | No. 12- 3D 22 1/2° | | No. 13- 3D 11 1/4° | |
|--------------------------|-------------------------|-----------------|---------------------|----------------|---------------------|-----------------|---------------------|----------------|---------------------|--------------------|---------------------|--------------------|---------------------|
| Nominal Outside Diameter | Actual Outside Diameter | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each |
| inches | mm | inches | lbs. | inches | lbs. | inches | lbs. | inches | lbs. | inches | lbs. | inches | lbs. |
| mm | mm | mm | kg | mm | kg | mm | kg | mm | kg | mm | kg | mm | kg |
| 2 | 2.375 | 10.00 | 5.3 | 7.50 | 4.3 | 6.50 | 3.9 | 5.75 | 3.4 | 5.25 | 3.2 | 4.50 | 2.8 |
| 50 | 60.3 | 254 | 2.4 | 191 | 2.0 | 165 | 1.8 | 146 | 1.5 | 133 | 1.5 | 114 | 1.3 |
| 2½ | 2.875 | 11.50 | 9.5 | 8.25 | 7.7 | 7.25 | 6.7 | 6.00 | 5.8 | 5.50 | 5.3 | 4.75 | 4.6 |
| 65 | 73.0 | 292 | 4.3 | 210 | 3.5 | 184 | 3.0 | 152 | 2.6 | 140 | 2.4 | 121 | 2.1 |
| 3 | 3.500 | 13.00 | 14.0 | 9.25 | 11.0 | 7.75 | 9.5 | 6.50 | 8.0 | 5.75 | 7.3 | 5.00 | 6.2 |
| 80 | 88.9 | 330 | 6.4 | 235 | 5.0 | 197 | 4.3 | 165 | 3.6 | 146 | 3.3 | 127 | 2.8 |
| 3½ | 4.000 | 14.50 | 18.6 | 10.00 | 14.4 | 8.50 | 12.3 | 6.75 | 10.2 | 6.00 | 9.2 | 5.00 | 7.6 |
| 90 | 101.6 | 368 | 8.4 | 254 | 6.5 | 216 | 5.6 | 172 | 4.6 | 152 | 4.2 | 127 | 3.4 |
| 4 | 4.500 | 16.00 | 24.1 | 11.00 | 18.5 | 9.00 | 15.7 | 7.25 | 12.8 | 6.50 | 11.4 | 5.25 | 9.3 |
| 100 | 114.3 | 407 | 10.9 | 279 | 8.4 | 229 | 7.1 | 184 | 5.8 | 165 | 5.2 | 133 | 4.2 |
| 4½ | 5.000 | 18.00 | 31.6 | 12.25 | 24.2 | 10.00 | 20.5 | 8.25 | 16.8 | 7.25 | 14.9 | 5.75 | 12.2 |
| 120 | 127.0 | 457 | 14.3 | 311 | 11.0 | 254 | 9.3 | 210 | 7.6 | 184 | 6.8 | 146 | 5.5 |
| 5 | 5.563 | 20.00 | 40.9 | 13.75 | 31.3 | 11.25 | 26.5 | 9.00 | 21.8 | 8.00 | 19.4 | 6.50 | 15.8 |
| 125 | 141.3 | 508 | 18.6 | 349 | 14.2 | 286 | 12.0 | 229 | 9.9 | 203 | 8.8 | 165 | 7.2 |
| 6 | 6.625 | 24.00 | 63.7 | 16.50 | 48.8 | 13.50 | 41.3 | 10.75 | 33.9 | 9.50 | 30.1 | 7.75 | 24.6 |
| 150 | 168.3 | 610 | 28.9 | 419 | 22.1 | 343 | 18.7 | 273 | 15.4 | 241 | 13.7 | 197 | 11.2 |
| 8 | 8.625 | 32.00 | 127.8 | 22.00 | 97.9 | 18.00 | 82.9 | 14.50 | 68.0 | 12.75 | 60.5 | 10.50 | 49.3 |
| 200 | 219.1 | 813 | 58.0 | 559 | 44.4 | 457 | 37.6 | 368 | 30.8 | 324 | 27.4 | 267 | 22.4 |
| 10 | 10.750 | 40.00 | 226.4 | 27.25 | 173.4 | 22.50 | 146.9 | 18.00 | 120.5 | 16.00 | 107.2 | 13.00 | 87.3 |
| 250 | 273.0 | 1016 | 102.7 | 692 | 78.7 | 572 | 66.6 | 457 | 54.7 | 406 | 48.6 | 330 | 39.6 |
| 12 | 12.750 | 48.00 | 332.7 | 32.75 | 254.8 | 27.00 | 215.9 | 21.75 | 177.0 | 19.25 | 157.5 | 15.50 | 128.3 |
| 300 | 323.9 | 1219 | 150.9 | 832 | 115.6 | 686 | 97.9 | 553 | 80.3 | 489 | 71.4 | 394 | 58.2 |
| 14 | 14.000 | 56.00 | 427.3 | 38.25 | 327.3 | 31.50 | 277.3 | 25.25 | 227.3 | 22.50 | 202.3 | 18.25 | 164.8 |
| 350 | 355.6 | 1422 | 193.8 | 972 | 148.5 | 800 | 125.8 | 641 | 103.1 | 572 | 91.8 | 464 | 74.8 |
| 15 | 15.000 | 60.00 | 480.8 | 41.00 | 368.3 | 33.75 | 312.0 | 27.00 | 255.8 | 24.00 | 227.6 | 19.50 | 185.4 |
| 375 | 381.0 | 1524 | 218.1 | 1041 | 167.1 | 857 | 141.5 | 656 | 116.0 | 610 | 103.2 | 495 | 84.1 |
| 16 | 16.000 | 64.00 | 560.1 | 43.75 | 429.0 | 36.00 | 363.5 | 29.00 | 297.9 | 25.50 | 265.2 | 20.75 | 216.0 |
| 400 | 406.4 | 1626 | 254.1 | 1111 | 194.6 | 914 | 164.9 | 737 | 135.1 | 648 | 120.3 | 527 | 98.0 |
| 18 | 18.000 | 72.00 | 710.7 | 49.25 | 544.4 | 40.50 | 461.3 | 32.50 | 378.1 | 28.75 | 336.5 | 23.25 | 274.1 |
| 450 | 457.2 | 1829 | 322.4 | 1251 | 246.9 | 1029 | 209.2 | 826 | 171.5 | 730 | 152.6 | 591 | 124.3 |
| 20 | 20.000 | 80.00 | 879.3 | 54.75 | 673.5 | 45.00 | 540.7 | 36.00 | 467.8 | 32.00 | 416.3 | 26.00 | 339.2 |
| 500 | 508.0 | 2032 | 398.9 | 1391 | 305.5 | 1143 | 245.3 | 914 | 212.2 | 813 | 188.8 | 660 | 153.9 |
| 22 | 22.000 | 88.00 | 1067.7 | 60.25 | 817.9 | 49.25 | 692.9 | 39.75 | 568.0 | 35.25 | 505.2 | 28.50 | 411.8 |
| 550 | 559.0 | 2235 | 484.3 | 1530 | 371.0 | 1251 | 314.3 | 1010 | 257.6 | 895 | 229.2 | 724 | 186.8 |
| 24 | 24.000 | 96.00 | 1270.3 | 65.50 | 973.0 | 53.75 | 824.4 | 43.25 | 675.7 | 38.25 | 601.4 | 31.00 | 490.0 |
| 600 | 609.6 | 2438 | 576.2 | 1664 | 441.4 | 1365 | 373.9 | 1099 | 306.5 | 972 | 272.8 | 787 | 222.3 |

General Notes

Long radius elbows (3D, 5D and 6D) in sizes up to and including 4" are provided with 4" integral tangent; remaining sizes provided with integral tangents with lengths equal to nominal pipe size.

Grooved or plain end available. Specify choice on order.


Bends to conform to above radii.

C to E tolerances: 2 - 6" ± 1/8"; 8 - 15" ± 1/4"; 16 - 24" ± 3/8"

All weights are approximate based on calculated weight of pipe.

Material: standard wall steel pipe to ASTM A-53 grade B (other materials available on request).

Long Radius Steel Elbows - 5D



No. 100 - 5D No. 14 - 5D No. 110 - 5D No. 15 - 5D No. 12 - 5D No. 13 - 5D

| Fitting Size | | No. 100- 5D 90° | | No. 14- 5D 60° | | No. 110- 5D 45° | | No. 15- 5D 30° | | No. 12- 5D 22 ½° | | No. 13- 5D 11 ¼° | |
|--------------------------|-------------------------|-----------------|---------------------|----------------|---------------------|-----------------|---------------------|----------------|---------------------|------------------|---------------------|------------------|---------------------|
| Nominal Outside Diameter | Actual Outside Diameter | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each |
| inches mm | inches mm | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg |
| 2 50 | 2.375 60.3 | 14.00 356 | 7.2 3.3 | 9.75 248 | 5.6 2.5 | 8.25 210 | 4.8 2.2 | 6.75 172 | 4.0 1.8 | 6.00 152 | 3.6 1.6 | 5.00 127 | 3.0 1.4 |
| 2½ 65 | 2.875 73.0 | 16.50 419 | 13.3 6.0 | 11.25 286 | 10.2 4.6 | 9.25 235 | 8.6 3.9 | 7.50 191 | 7.0 3.2 | 6.50 165 | 6.2 2.8 | 5.25 133 | 5.0 2.3 |
| 3 80 | 3.500 88.9 | 19.00 488 | 19.9 9.0 | 12.75 324 | 15.0 6.8 | 10.25 260 | 12.5 5.7 | 8.00 203 | 10.0 4.5 | 7.00 178 | 8.8 4.0 | 5.50 140 | 6.9 3.1 |
| 3½ 90 | 4.000 101.6 | 21.50 546 | 26.9 12.2 | 14.25 362 | 20.0 9.1 | 11.25 286 | 16.5 7.5 | 8.75 222 | 13.0 5.9 | 7.50 191 | 11.3 5.1 | 5.75 146 | 8.7 3.9 |
| 4 100 | 4.500 114.3 | 24.00 610 | 35.4 16.1 | 15.50 394 | 26.0 11.8 | 12.50 318 | 21.3 9.7 | 9.50 241 | 16.6 7.5 | 8.00 203 | 14.3 6.5 | 6.00 152 | 10.7 4.9 |
| 4½ 120 | 5.000 127.0 | 27.00 686 | 46.3 21.0 | 17.50 445 | 34.0 15.4 | 13.75 349 | 27.9 12.7 | 10.50 267 | 21.7 9.8 | 9.00 229 | 18.6 8.4 | 6.75 172 | 14.0 6.4 |
| 5 125 | 5.563 141.3 | 30.00 762 | 60.0 27.2 | 19.50 495 | 44.1 20.0 | 15.50 394 | 36.1 16.4 | 11.75 299 | 28.1 12.7 | 10.00 254 | 24.1 10.9 | 7.50 191 | 18.2 8.3 |
| 6 150 | 6.625 168.3 | 36.00 914 | 93.5 42.4 | 23.25 591 | 68.6 31.1 | 18.50 470 | 56.2 25.5 | 14.00 356 | 43.8 19.9 | 12.00 305 | 37.6 17.1 | 9.00 229 | 28.3 12.8 |
| 8 200 | 8.625 219.1 | 48.00 1219 | 187.6 85.1 | 31.00 787 | 137.7 62.5 | 24.50 622 | 112.8 51.2 | 18.75 476 | 87.9 39.9 | 16.00 406 | 75.4 34.2 | 12.00 305 | 56.8 25.8 |
| 10 250 | 10.750 273.0 | 60.00 1524 | 332.4 150.8 | 39.00 991 | 244.1 110.7 | 30.75 781 | 199.9 90.7 | 23.50 597 | 155.8 70.7 | 20.00 5008 | 133.7 60.6 | 15.00 381 | 100.6 45.6 |
| 12 300 | 12.750 323.9 | 72.00 1829 | 488.4 221.5 | 46.75 1188 | 358.6 162.7 | 37.00 940 | 293.7 133.2 | 28.00 711 | 228.9 103.8 | 24.00 610 | 196.4 89.1 | 18.00 457 | 147.8 67.0 |
| 14 350 | 14.000 355.6 | 84.00 2134 | 627.4 284.6 | 54.50 1384 | 460.7 209.0 | 43.00 1092 | 377.3 171.1 | 32.75 832 | 294.0 133.4 | 28.00 711 | 252.3 114.4 | 21.00 533 | 189.8 86.1 |
| 15 375 | 15.000 381.0 | 90.00 2286 | 705.8 320.2 | 58.25 1498 | 518.3 235.1 | 46.00 1168 | 424.6 192.6 | 35.25 895 | 330.8 150.1 | 30.00 762 | 283.9 128.8 | 22.50 572 | 213.6 96.6 |
| 16 400 | 16.000 406.4 | 96.00 2438 | 822.2 372.9 | 62.25 1581 | 603.8 273.9 | 49.25 1251 | 494.5 224.3 | 37.50 953 | 385.3 174.8 | 32.00 813 | 330.7 150.0 | 24.00 610 | 248.8 112.9 |
| 18 450 | 18.000 457.2 | 108.00 2743 | 1043.4 473.3 | 70.00 1778 | 766.2 347.5 | 55.25 1403 | 627.6 284.7 | 42.25 1073 | 489.0 221.8 | 36.00 914 | 419.7 190.4 | 27.00 686 | 315.7 143.2 |
| 20 500 | 20.000 508.0 | 120.00 3048 | 1290.9 585.6 | 77.75 1975 | 947.9 430.0 | 61.50 1562 | 776.4 352.2 | 46.75 1188 | 605.0 274.4 | 40.00 1016 | 519.2 235.5 | 30.00 762 | 390.6 177.2 |
| 22 550 | 22.000 559.0 | 132.0 3353 | 1567.4 711.0 | 85.50 2172 | 1150.9 522.0 | 67.50 1715 | 942.7 427.6 | 51.50 1308 | 734.6 333.2 | 44.00 1118 | 630.5 286.0 | 32.75 832 | 474.3 215.1 |
| 24 600 | 24.000 609.6 | 144.00 3658 | 1864.8 845.9 | 93.25 2369 | 1369.3 621.1 | 73.75 1873 | 1121.6 508.8 | 56.25 1429 | 873.9 396.4 | 48.00 1219 | 750.1 340.2 | 35.75 908 | 564.3 256.0 |

General Notes

Long radius elbows (3D, 5D and 6D) in sizes up to and including 4" are provided with 4" integral tangent; remaining sizes provided with integral tangents with lengths equal to nominal pipe size.

Grooved or plain end available. Specify choice on order.


Bends to conform to above radii.

C to E tolerances: 2 - 6" ± 1/8"; 8 - 15" ± 1/4"; 16 - 24" ± 3/8"

All weights are approximate based on calculated weight of pipe.

Material: standard wall steel pipe to ASTM A-53 grade B (other materials available on request).

Long Radius Steel Elbows - 6D



No. 100 - 6D No. 14 - 6D No. 110 - 6D No. 15 - 6D No. 12 - 6D No. 13 - 6D

| Fitting Size | | No. 100- 6D 90° | | No. 14- 6D 60° | | No. 110- 6D 45° | | No. 15- 6D 30° | | No. 12- 6D 22 ½° | | No. 13- 6D 11 ¼° | |
|--------------------------|-------------------------|-----------------|---------------------|----------------|---------------------|-----------------|---------------------|----------------|---------------------|------------------|---------------------|------------------|---------------------|
| Nominal Outside Diameter | Actual Outside Diameter | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each | C to E | Approx. Weight Each |
| inches mm | inches mm | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg | inches mm | lbs. kg |
| 2 | 2.375 | 16.00 | 8.2 | 11.00 | 6.3 | 9.00 | 5.3 | 7.25 | 4.3 | 6.50 | 3.9 | 5.25 | 3.2 |
| 50 | 60.3 | 406 | 3.7 | 279 | 2.9 | 229 | 2.4 | 184 | 2.0 | 165 | 1.8 | 133 | 1.5 |
| 2½ | 2.875 | 19.00 | 15.2 | 12.75 | 11.4 | 10.25 | 9.5 | 8.00 | 7.7 | 7.00 | 6.7 | 5.50 | 5.3 |
| 65 | 73.0 | 483 | 6.9 | 324 | 5.2 | 260 | 4.3 | 203 | 3.5 | 178 | 3.0 | 140 | 2.4 |
| 3 | 3.500 | 22.00 | 22.9 | 14.50 | 17.0 | 11.50 | 14.0 | 8.75 | 11.0 | 7.50 | 9.5 | 5.75 | 7.3 |
| 80 | 88.9 | 559 | 10.4 | 368 | 7.7 | 292 | 6.4 | 222 | 5.0 | 191 | 4.3 | 146 | 3.3 |
| 3½ | 4.000 | 25.00 | 31.1 | 16.25 | 22.8 | 12.75 | 18.6 | 9.75 | 14.4 | 8.25 | 12.3 | 6.00 | 9.2 |
| 90 | 101.6 | 635 | 14.1 | 413 | 10.3 | 324 | 8.4 | 248 | 6.5 | 210 | 5.6 | 152 | 4.2 |
| 4 | 4.500 | 28.00 | 41.1 | 18.00 | 29.8 | 14.00 | 24.1 | 10.50 | 18.5 | 8.75 | 15.7 | 6.50 | 11.4 |
| 100 | 114.3 | 711 | 18.6 | 457 | 13.5 | 356 | 10.9 | 267 | 8.4 | 222 | 7.1 | 165 | 5.2 |
| 4½ | 5.000 | 31.50 | 53.7 | 20.00 | 39.0 | 15.75 | 31.6 | 11.75 | 24.2 | 10.00 | 20.5 | 7.25 | 14.9 |
| 120 | 127.0 | 800 | 24.4 | 508 | 17.7 | 400 | 14.3 | 299 | 11.0 | 254 | 9.3 | 184 | 6.8 |
| 5 | 5.563 | 35.00 | 69.6 | 22.25 | 50.5 | 17.50 | 40.9 | 13.00 | 31.3 | 11.00 | 26.5 | 8.00 | 19.4 |
| 125 | 141.3 | 889 | 31.6 | 565 | 22.9 | 445 | 18.6 | 330 | 14.2 | 279 | 12.0 | 203 | 8.8 |
| 6 | 6.625 | 42.00 | 108.4 | 26.75 | 78.6 | 21.00 | 63.7 | 15.75 | 48.8 | 13.25 | 41.3 | 9.50 | 30.1 |
| 150 | 168.3 | 1067 | 49.2 | 680 | 35.7 | 533 | 28.9 | 400 | 22.1 | 337 | 18.7 | 241 | 13.7 |
| 8 | 8.625 | 56.00 | 217.5 | 35.75 | 157.7 | 28.00 | 127.8 | 21.00 | 97.9 | 17.50 | 82.9 | 12.75 | 60.5 |
| 200 | 219.1 | 1422 | 98.7 | 908 | 71.5 | 711 | 58.0 | 533 | 44.4 | 445 | 37.6 | 324 | 27.4 |
| 10 | 10.750 | 70.00 | 385.4 | 44.75 | 279.4 | 35.00 | 226.4 | 26.00 | 173.4 | 22.00 | 146.9 | 16.00 | 107.2 |
| 250 | 273.0 | 1778 | 174.8 | 1137 | 126.7 | 889 | 102.7 | 660 | 78.7 | 559 | 66.6 | 406 | 48.6 |
| 12 | 12.750 | 84.00 | 566.2 | 53.50 | 410.5 | 41.75 | 332.7 | 31.25 | 254.8 | 26.25 | 215.9 | 19.00 | 157.5 |
| 300 | 323.9 | 2134 | 256.8 | 1359 | 186.2 | 1061 | 150.9 | 794 | 115.6 | 667 | 97.9 | 483 | 71.4 |
| 14 | 14.000 | 98.00 | 727.4 | 62.50 | 527.3 | 48.75 | 427.3 | 36.50 | 327.3 | 30.75 | 277.3 | 22.25 | 202.3 |
| 350 | 355.6 | 2489 | 329.9 | 1588 | 239.2 | 1238 | 193.8 | 927 | 148.5 | 781 | 125.8 | 565 | 91.8 |
| 15 | 15.000 | 105.00 | 818.4 | 67.00 | 593.3 | 52.25 | 480.2 | 39.25 | 386.3 | 33.00 | 312.0 | 24.00 | 227.6 |
| 375 | 381.0 | 2667 | 371.2 | 1702 | 269.1 | 1327 | 217.8 | 997 | 167.1 | 838 | 141.5 | 609 | 103.2 |
| 16 | 16.000 | 112.00 | 953.3 | 71.50 | 691.1 | 55.75 | 560.1 | 41.75 | 429.0 | 35.25 | 363.5 | 25.50 | 265.2 |
| 400 | 406.4 | 2845 | 432.4 | 1816 | 313.5 | 1416 | 254.1 | 1061 | 194.6 | 895 | 164.9 | 648 | 120.3 |
| 18 | 18.000 | 126.00 | 1209.7 | 80.50 | 877.1 | 62.75 | 710.7 | 47.00 | 544.4 | 39.50 | 461.3 | 28.75 | 336.5 |
| 450 | 457.2 | 3200 | 548.7 | 2045 | 397.9 | 1594 | 322.4 | 1194 | 246.9 | 1003 | 209.2 | 730 | 152.6 |
| 20 | 20.000 | 140.00 | 1496.6 | 89.25 | 1085.1 | 69.75 | 879.3 | 52.25 | 673.5 | 44.00 | 570.7 | 31.75 | 416.3 |
| 500 | 508.0 | 3556 | 678.9 | 2267 | 492.2 | 1772 | 398.9 | 1327 | 305.5 | 1118 | 258.9 | 807 | 188.8 |
| 22 | 22.000 | 154.00 | 1817.3 | 98.25 | 1317.5 | 76.75 | 1067.7 | 57.50 | 817.9 | 48.25 | 693.0 | 35.00 | 505.5 |
| 550 | 559.0 | 3912 | 824.3 | 2496 | 597.6 | 1950 | 484.3 | 1461 | 371.0 | 1256 | 314.3 | 889 | 229.3 |
| 24 | 24.000 | 168.00 | 2162.8 | 107.25 | 1567.5 | 83.75 | 1270.3 | 62.50 | 973.0 | 52.75 | 824.4 | 38.25 | 601.4 |
| 600 | 609.6 | 4267 | 980.7 | 2724 | 711.0 | 2127 | 576.2 | 1588 | 441.4 | 1340 | 373.9 | 972 | 272.8 |

General Notes

Long radius elbows (3D, 5D and 6D) in sizes up to and including 4" are provided with 4" integral tangent; remaining sizes provided with integral tangents with lengths equal to nominal pipe size.

Grooved or plain end available. Specify choice on order.

Bends to conform to above radii.

C to E tolerances: 2 - 6" ± 1/8"; 8 - 15" ± 1/4"; 16 - 24" ± 3/8"

All weights are approximate based on calculated weight of pipe.

Material: standard wall steel pipe to ASTM A-53 grade B (other materials available on request).

Installation

Reference should always be made to the [I-100 Victaulic Field Installation Handbook](#) for the product you are installing. Handbooks are included with each shipment of Victaulic products for complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Trademarks

Victaulic® is a registered trademark of Victaulic Company.