

# Style 155 Expansion Joint Application Data Sheet

## PRODUCT DESCRIPTION



Style 155 Expansion Joints are a combination of couplings and specially machined pipe nipples, joined in series to accommodate piping system expansion/contraction.

The standard units are assembled with either Style 77 or Style 75 flexible couplings. The following information is required for processing all requests for Style 155 Expansion Joints. All sections of the data form below must be completed to ensure performance requirements are satisfied.

**Fax this form with purchase order to Engineered Products Division at 610/923-3010.**

SALESMAN / DISTRIBUTOR / BRANCH CONTACT:		PROJECT REFERENCE:	
<b>PIPE SPECIFICATION:</b>			
NOMINAL DIA.:	ACTUAL DIA.:	WALL THICKNESS:	MATERIAL:
PIPE COATING: <input type="checkbox"/> Uncoated <input type="checkbox"/> Galvanized <input type="checkbox"/> Other _____ (Attach specification)			
PIPE END NIPPLES: <input type="checkbox"/> Grooved <input type="checkbox"/> Plain <input type="checkbox"/> Beveled <input type="checkbox"/> Threaded ( <input type="checkbox"/> BSP <input type="checkbox"/> NPT ) <input type="checkbox"/> Flanged (Class _____)			
<b>SYSTEM OPERATING PARAMETERS:</b>			
SERVICE:		MAX. WORKING PRESSURE:	MAX. OPERATING TEMP.:
COUPLING COATING: <input type="checkbox"/> Painted <input type="checkbox"/> Galvanized <input type="checkbox"/> Other _____ (Attach specification)			
BOLT/NUT SPECIFICATION: <input type="checkbox"/> Standard <input type="checkbox"/> Metric		BOLT MATERIAL: <input type="checkbox"/> Carbon Steel <input type="checkbox"/> Stainless Steel	
<b>SYSTEM EXPANSION/CONTRACTION REQUIREMENTS:</b>			
MAXIMUM PIPE EXPANSION:		MAXIMUM PIPE CONTRACTION:	
<b>ORDERING INFORMATION:</b>		QUANTITY REQUIRED:	DATE REQUIRED:
<b>SPECIAL PACKAGING REQUIREMENTS:</b>			

***For Internal Use Only!!!***

ORDER NUMBER:	PART CODE NO.:	ENGINEERING CONTACT:
COUPLING STYLE: <input type="checkbox"/> S/77 <input type="checkbox"/> S/75 <input type="checkbox"/> Other _____		GASKET MATERIAL: <input type="checkbox"/> E <input type="checkbox"/> T <input type="checkbox"/> O <input type="checkbox"/> L <input type="checkbox"/> V <input type="checkbox"/> Other _____
NUMBER OF COUPLINGS:	NUMBER OF NIPPLES:	GASKET TYPE: <input type="checkbox"/> Standard <input type="checkbox"/> FlushSeal®
PIPE END NIPPLES: <input type="checkbox"/> Grooved <input type="checkbox"/> Plain <input type="checkbox"/> Beveled <input type="checkbox"/> Threaded ( <input type="checkbox"/> BSP <input type="checkbox"/> NPT ) <input type="checkbox"/> Flanged (Class _____)		
PIPE END NIPPLE LENGTH: <input type="checkbox"/> Standard <input type="checkbox"/> Other _____		PIPE SCHEDULE: <input type="checkbox"/> Std. Wgt. <input type="checkbox"/> Hvy. Wgt. <input type="checkbox"/> Special _____
EXPANSION JOINT TO BE SUPPLIED IN: <input type="checkbox"/> Fully Expanded Position <input type="checkbox"/> Fully Contracted Position <input type="checkbox"/> Other _____		

Contact Victaulic for additional assistance with applications requiring pipe movement compensation.