



Victaulic Vortex™ Fire Suppression System



SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS



**SERIES 951
FLUID BOX**



**SERIES 951
ZONE BOX**

PRODUCT DESCRIPTION

In the zoned configuration, a single Victaulic Vortex System is capable of providing fire suppression for multiple hazards. A zoned system uses a single Series 951 Fluid Box and any number of Series 951 Zone Boxes to direct the flow of nitrogen and water to the appropriate hazard. The system requires a single nitrogen source that is sized for the largest hazard. The water supply can be local to each Zone Box or shared as a common resource for the entire system.

The Series 951 Fluid Box contains an Automated Regulating Valve (ARV) that is coupled with a pressure transducer to maintain a fixed system pressure as the supply pressure decays. The inlet for the Fluid Box is connected to a single nitrogen source while the outlet is connected to a common header that provides each Zone Box with a nitrogen supply.

Each Series 951 Zone Box contains an automated ball valve to control the on/off flow of nitrogen to the hazard. The nitrogen connection inlet for the Zone Box is connected to a common regulated nitrogen source created by the outlet from the Fluid Box. The outlet of the Zone Box feeds the emitter array. The Zone Box also contains either a ball valve or solenoid (flow-rate dependent) to control the on/off flow of water to the hazard. The water inlet to the Zone Box is connected to an independent or shared source while the outlet is connected to the system emitter array. The water piping in each box contains a serviceable "Y type" strainer and supervised isolation valve to provide ease of maintenance.

The Victaulic Vortex zoned system requires the use of an addressable FM Approved agent release panel to control the system's operation. Delay and soak timer features will be applied to control the operation of each box. The electrical interface for the system is comprised of clearly labeled, color-coded, push-to-connect terminal blocks that simplify system installation

All necessary plumbing protrusions are factory made to provide supply connections from the side or bottom of the enclosure. The drain and nitrogen supply connection will be threaded and require proper pipe schedules to be used. The inlet or outlet piping and water supply will be grooved to accept Victaulic couplings and is sized to 1"/25 mm, 1 1/2"/38 mm or 2"/50 mm depending upon system design.

JOB/OWNER

System No. _____
Location _____

CONTRACTOR

Submitted By _____
Date _____

ENGINEER

Spec Sect _____ Para _____
Approved _____
Date _____

www.victaulic.com


VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. VICTAULIC VORTEX IS A TRADEMARK OF VICTAULIC COMPANY.
© 2011 VICTAULIC COMPANY. ALL RIGHTS RESERVED.



Victaulic Vortex™ Fire Suppression System

SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS

DIMENSIONS FLUID BOX




Description	A	B	C	D	Aprox. Weight lbs/kg
Fluid Control Box, Dry Contact, 1-inch Assembly	1.68" 42.7 mm	1" NPT	1" NPT	1" grooved	130 59
Fluid Control Box, Dry Contact, 1 1/2-inch Assembly	2.20" 56.0 mm	1 1/2" NPT	1 1/2" NPT	1 1/2" grooved	140 64

Victaulic Vortex™ Fire Suppression System

SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS

DIMENSIONS ZONE BOX



Description	Dimensions – inches/mm											L	M	Aprox. Weight lbs/kg
	A	B	C	D	E	F	G	H	J	K				
Zone Control Box, Dry Contact, Solenoid Valve Release, 1-inch Assembly	24.00 609.6	24.00 609.6	4.38 111.3	10.50 266.7	2.80 71.1	1.88 47.6	32.11 815.6	7.62 193.5	1.07 27.1	2.79 71.0	1" grooved	1" grooved	130 59	
Zone Control Box, Dry Contact, Ball Valve Release, 1-inch Assembly	24.00 609.6	24.00 609.6	4.38 111.3	10.50 266.7	2.80 71.1	1.88 47.6	32.11 815.6	7.62 193.5	1.18 29.8	3.01 76.5	1" grooved	1" grooved	140 64	
Zone Control Box, Dry Contact, Solenoid Valve Release, 1 ½-inch Assembly	30.00 762.0	30.00 762.0	6.00 152.4	13.00 330.2	3.55 90.2	3.49 88.6	38.11 968.0	9.50 241.3	1.53 38.7	2.66 67.6	1 ½" grooved	1 ½" grooved	140 64	
Zone Control Box, Dry Contact, Ball Valve Release, 1 ½-inch Assembly	30.00 762.0	30.00 762.0	6.00 152.4	13.00 330.2	3.55 90.2	3.49 88.6	38.11 968.0	9.50 241.3	1.18 29.8	3.01 76.5	1 ½" grooved	1 ½" grooved	150 68	
Zone Control Box, Dry Contact, Ball Valve Release, 2-inch Assembly	30.00 762.0	30.00 762.0	6.00 152.4	13.00 330.2	3.55 90.2	3.49 88.6	38.11 968.0	9.50 241.3	1.44 36.4	1.61 40.9	2" grooved	2" grooved	150 68	

www.victaulic.com

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. VICTAULIC VORTEX IS A TRADEMARK OF VICTAULIC COMPANY. © 2011 VICTAULIC COMPANY. ALL RIGHTS RESERVED.



REV_A

70.08_3

Victaulic Vortex™ Fire Suppression System

SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS

MATERIAL SPECIFICATIONS FLUID AND ZONE BOXES

Cabinet Specifications: Carbon steel, 14 gauge

Finish: Cabinet, polyester powdered coated red

Back panel: Zinc plated for corrosion resistance

Automatic Regulating Valve:

Body: UNS C954000 aluminum bronze

Seal: Ultra-high molecular weight polyethylene

Stem and Seal Retainer: UNS 416 stainless steel

Stem Adapter: UNS C36000 brass or UNS C95400 aluminum bronze

Manifold Blocks: Low carbon steel

Strainer: Brass with UNS 302000 stainless steel screen

PERFORMANCE DATA FLUID BOX

Pressure Inputs:

Nitrogen: 3000 psi/20684 kPa

Pressure Outputs:

Nitrogen: 150 psi/1034 kPa

Temperature ratings: 40°F/4°C to 130°F/55°C

ELECTRICAL SPECIFICATIONS FLUID BOX

Title: Connected in the middle of the release signal from FACP and the solenoid at the primary head

Operation Voltage: 24VDC continuous power supply (23-27VDC), polarity sensitive

Alarm Current: 2 Amps

Standby Current: 125mA

Supervisory Connections: 500mA @30 VDC resistive load

Pressure Transducer:

Operation Voltage: 24VDC, polarity sensitive

Output: 4-20mA (0-50 psi/0-335 kPa, 0-100 psi/0-689 kPa, 0-300 psi/0-2068 kPa)

Connections: 18 AWG shielded twisted pair

Victaulic Vortex™ Fire Suppression System

SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS

CONNECTIONS FLUID BOX

DC Power – TB1

- 23-27 VDC operation voltage
- Supervised by system fault contact

Transducer – TB2

- Polarity sensitive
- Uses supply power from TB1
- Shield connection terminated at panel only
- Operation and wiring supervised by system fault contact

Supervisory – TB3

- System fault connection (24V, transducer, PLC fault)
- Provides the means to signal a system fault to another device
- Manifold charge
- 500mA @ 30VDC resistive dry contacts
- Non-latching

Release Input – TB4

- Termination point from release panel
- Two connections, Release + and Release -

Solenoid Output – TB5

- Out to primary head
- Optional second head connection
- 22-27 VDC operation voltage
- 13 Watts

CONTROLS AND INDICATORS FLUID BOX

Multifunction Key Switch

- Disables ARV from operating (Primary release circuit shall include a separate disable switch)
- Resets valve after discharge
- Key removal in normal, ready condition
- Closes system fault contact

Red Indicator Light

- Visual indicator that system is in the not ready condition
- Active when system fault contact is closed
- Light is off in normal condition

Pressure Gauge

- Provides visual indication of manifold pressure
- 0-4000 psi/0-27579 kPa
- Reference only gauge

PERFORMANCE DATA ZONE BOX

Pressure Inputs:

Nitrogen: 150 psi/1034 kPa

Water: 300 psi/2068 kPa

Pressure Outputs:

Nitrogen: 150 psi/1207 kPa

Water: 300 psi/2068 kPa

Temperature Ratings: 40°F/4°C to 130°F/55°C

www.victaulic.com

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. VICTAULIC VORTEX IS A TRADEMARK OF VICTAULIC COMPANY.
© 2011 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

REV_A



70.08_5

Victaulic Vortex™ Fire Suppression System

SERIES 951 FLUID AND SERIES 951 ZONE CONTROL BOXES FOR USE WITH VICTAULIC
VORTEX 1000 AND VICTAULIC VORTEX 1500 FIRE SUPPRESSION SYSTEMS

ELECTRICAL SPECIFICATIONS ZONE BOX

Operation Voltage: 24VDC continuous power supply (23-27VDC), polarity sensitive

Alarm Current: 2 Amps

Standby Current: 22mA

Supervisory Connections: 500mA @30 VDC resistive load

CONNECTIONS ZONE BOX

DC Power – TB1

- 23-27 VDC Operation Voltage
- Supervised By System Fault Contact

Release – TB2

- Nitrogen valve, 350 ohm
- Water valve, 350 ohm

Supervisory – TB3

- System fault connection, 24V
- Provides the means to signal a system fault to another device
- Water isolation valve
- 500mA @ 30VDC resistive dry contacts

INSTALLATION

Reference should always be made to the applicable I-VORTEX Victaulic Field Installation Handbook for the product you are installing. Handbooks are included with each shipment of Victaulic products for complete installation and assembly data.

WARRANTY

Refer to the Warranty section of the current Price List or contact Victaulic for details.

NOTE

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

For complete contact information, visit www.victaulic.com

70.08 6353 REV A UPDATED 11/2011

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. VICTAULIC VORTEX IS A TRADEMARK OF VICTAULIC COMPANY.
© 2011 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

70.08

