

CERTIFICATE OF CONFORMANCE

Victaulic® is an ISO 9001 certified company. Our standard materials conform to the following ASTM, ASME or ISO standards as applicable:

CASTINGS

Ductile Iron: ASTM A536 – Grade 65-45-12

Stainless Steel: ASTM A351, ASTM A743 or ASTM A744 – Grade CF8M or CF8
ASTM A890 – Grade 2A CE8MN or Grade 5A CE3MN

Aluminum: ASTM B26 – Alloy 356-T6

Copper: ASTM B584 – Alloy C89836 or C87850

Carbon Steel: ASTM A216 – Grade WCB

FABRICATIONS

Carbon Steel: ASTM A53 – Type F or Type E or S Grade B
ASTM A234 – Grade WPB
ASTM A108 – Grade 1018
ASTM A36

Stainless Steel: ASTM A312 – Grade TP304L or TP316L
ASTM A403 – Grade WP304L, CR304L, WP316L or CR316L
ASTM A240 – S30403, S31600, or S31603
ASTM A276 – S31600

Aluminum: ASTM B241 – Alloy 6061-T6 or 6063-T6
ASTM B210 – Alloy 6061-T6 or 6063-T6

Copper: ASTM B75 – Alloy C12200
ASTM B152 – Alloy C11000

GASKETS

ASTM D2000

NUTS AND BOLTS

Carbon Steel: ASTM A449 and ASTM A563 – Grade A or B
ISO 898-1 Part 1 – Class 9.8 or 8.8 and ASTM A563M – Class 9

Stainless Steel: ASTM A193 – Class 2, Grade B8M and ASTM A194 – Grade 8M, Heavy Hex
ASTM F738M – Class A4-80 and ASTM F836M – Class A4-80
ASTM F593 – Group 2, Condition CW, Alloy 316 and
ASTM F594 – Group 2, Condition CW, Alloy 316
ISO 3506 – Grade A4-80 or A4-70

VIC RINGS

ASME SA105 / ASTM A105 or ASME SA105N / ASTM A105N

GALVANIZING

ASTM A153 or ASTM A123

ZINC ELECTROPLATING

ASTM B633 or ASTM F1941

Very truly yours,



J.R. Van Wert
Director – Global Quality

4901 Kesslersville Road | Easton PA 18040

For complete contact information, visit www.victaulic.com.

02.05 7094 REV C UPDATED 04/2013

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2013 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

