

**TYPE APPROVAL CERTIFICATE****This is to certify:****That the Butterfly Valves**with type designation(s)  
**Vic-300 Masterseal Series 761**Issued to  
**Victaulic Company**  
**Easton PA, USA**is found to comply with  
**DNV GL rules for classification – Ships Pt.4 Ch.6 Piping systems**  
**DNV GL class programme DNVGL-CP-0186 – Type approval – Valves**  
**DNVGL-OS-D101 – Marine and machinery systems and equipment, Edition July 2015****Application :****Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV GL.****Temperature range: 0°C – 120°C (see page 2)**  
**Max. working press.: 232 psi (16 bar)**  
**Sizes: 2" to 12" (see page 2)**Issued at **Høvik** on **2017-12-13**for **DNV GL**This Certificate is valid until **2022-06-30**.DNV GL local station: **New York**Approval Engineer: **Sinisa Sedlan**

---

**Marianne Spæren Marveng**  
**Head of Section**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



Job Id: **262.1-013258-4**  
Certificate No: **TAP000012D**

## Product description

Butterfly valves type VIC®-300 MasterSeal™ Series 761 with grooved ends for use with grooved pipe couplings, and with standard ISO mounting flange to accept most gear and power actuators.

Sizes: 2" (DN50), 2½" (DN65), 76.1 mm, 3" (DN80), 108.0 mm, 4" (DN100), 133.0 mm, 139.7 mm, 5" (DN125), 159.0 mm, 165.1 mm, 6" (DN150), 8" (DN200), 10" (DN250), 12" (DN300)

### Materials:

Body	ASTM A536 65-45-12 (ferritic/pearlitic nodular cast iron)
Disc	ASTM A536 65-45-12 with nickel coating to ASTM B-733, Ni-Al bronze Alloy C95500, ASTM A-351 CF8M
Stem	ASTM A582 416, ASTM A564 17-4PH
Seat	EPDM, Nitrile, Fluorelastomer

### Manufacturing locations:

Victaulic Easton Facility  
4901 Kesslersville Road  
Easton, PA 18040 – USA

Victaulic Polska Facility  
STR Niepodleglosci 8  
66-530 Drezdenko  
Prov. Gorzow, Poland

Dalian Bingshan Metal Technology Co., Ltd (DBMT)  
No 9 Northeast 7<sup>th</sup> Street  
Dalian Economy & Technology Developing Zone  
Dalian 116600 China

Victaulic Piping Products (Dalian) Co. Ltd. (VPP)  
No. 13 Tie Shan Dong 2 Road  
Dalian Development Area  
Dalian 116630 China

## Application/Limitation

The approval is valid for ship, machinery & cargo piping systems onboard DNV GL classed ships and mobile offshore units.

### Design temperatures depending on seat materials:

EPDM/Fluoroelastomer: 0°C to +120°C  
Nitrile: 0°C to +82°C

### Valves covered by this certificate shall not be used in:

- Class I and II piping systems, except in hydraulic piping systems where failure would not render the system inoperative or introduce a fire risk
- Piping subject to pressure shock, excessive strains and vibration
- Ship's side or bottom and on sea chest
- Collision bulkheads
- Under static head fitted on external wall of tanks for fuel and flammable oils
- Ballast lines to forward tanks through cargo oil tanks
- Bilge and ballast piping in tunnels in double bottom
- Seawater applications

- Media having temperature below 0°C and above 120 °C
- As shut off or quick closing valves

Valves covered by this certificate with non-metallic seats are not to be considered fire safe and shall not be installed in systems where fire safe applications are required.

The approval does not include any operating gear for remote control of the valves.

This certificate does not cover valves installed in LNG/LPG applications.

## Type Approval documentation

### Drawings:

V-020-761-312 Rev.P	H-020-761-300 Rev.G	H-020-761-301 Rev.G	H-024-761-300 Rev.F
H-024-761-301 Rev.I	H-030-761-300 Rev.F	H-030-761-301 Rev.I	H-040-761-300 Rev.G
H-040-761-301 Rev.H	H-050-761-300 Rev.E	H-050-761-301 Rev.I	H-060-761-300 Rev.G
H-060-761-301 Rev.P	H-080-761-300 Rev.J	H-080-761-301 Rev.G	H-100-761-300 Rev.D
H-100-761-301 Rev.E	H-108-761-300 Rev.E	H-108-761-301 Rev.F	H-120-761-300 Rev.F
H-120-761-301 Rev.E	H-133-761-300 Rev.E	H-133-761-301 Rev.F	H-139-761-300 Rev.E
H-139-761-301 Rev.H	H-159-761-300 Rev.E	H-159-761-301 Rev.G	H-165-761-300 Rev.E
H-165-761-301 Rev.H	H-761-761-300 Rev.E	H-761-761-301 Rev.G	P-020-761-302 Rev.D
P-020-761-303 Rev.D	P-024-761-302 Rev.B	P-024-761-303 Rev.D	P-030-761-302 Rev.B
P-030-761-303 Rev.C	P-040-761-302 Rev.B	P-040-761-303 Rev.E	P-050-761-302 Rev.B
P-050-761-303 Rev.B	P-060-761-302 Rev.C	P-060-761-303 Rev.D	P-108-761-302 Rev.D
P-108-761-303 Rev.D	P-133-761-302 Rev.D	P-133-761-303 Rev.D	P-139-761-302 Rev.B
P-139-761-303 Rev.C	P-159-761-302 Rev.D	P-159-761-303 Rev.E	P-165-761-302 Rev.B
P-165-761-303 Rev.D	P-761-761-302 Rev.B	P-761-761-303 Rev.B	

Calculation sheet EN12516 Tables for S761 S716

## Production Testing

Each valve body shall be subjected to a hydrostatic pressure test at 1.5 times the maximum allowable working pressure at room temperature.

In addition each valve shall be subjected to seat leakage testing at 1.1 times maximum allowable working pressure at closed position.

Testing shall follow procedures and acceptance criteria in EN12266-1 (leakage rate A).

Production testing for valves that require DNV GL product certificate shall be witnessed by DNV GL surveyor.

## Certification

DNV GL product certificate is required for valves with DN>100 mm and design pressure  $\geq$  16 bar. Otherwise manufacturer's product certificate may be accepted.

Material certificates for valve bodies shall be according to DNV GL Pt.4 Ch.6 Sec.2 Table 3.

Job Id: **262.1-013258-4**  
Certificate No: **TAP000012D**

## Marking of product

For traceability to this type approval the valves are to be marked as a minimum with:

- Manufacturers name or trade mark
- Valve type designation
- Size
- Maximum design pressure and temperature

## Periodical assessment

For retention of the Type Approval, a DNV GL Surveyor shall perform periodical assessment every second year and before the expiry date of this certificate, to verify that the conditions for the type approval are complied with.

When possible, this assessment may be harmonised with normal surveys for product certification and / or other surveys and audits carried out.

The main elements of the certificate retention survey are:

- Verification of the TA applicant's production and quality system w.r.t. ensuring continued
- consistent production of the type approved products at the TA applicant's own premises
- Review of Type Approval documentation and assurance that it is still used as basis for production
- Review of possible changes in design, materials and performance
- Assurance of traceability between manufacturer's product type marking and Type Approval Certificate.

Renewal should be applied for in writing before the certificate expires.